

NBP1-22496**Blood Group Kell Antigen Antibody (RM0118-7L32)****Unit Size**

0.1 mg

Concentration

lyoph

Storage

Aliquot and store at -20C or -80C. Avoid freeze-thaw cycles.

Applications

WB

Species

Mouse

Host

Rat

Clonality

Monoclonal

Isotype

IgG2

Purity

Protein G purified

Preservative

Sodium Azide

Specificity/Sensitivity

This was produced from a hybridoma (mouse myeloma) fused with spleen cells from a rat immunized with mouse recombinant protein of extracellular domain of Kell (CD238).

Immunogen

Mouse recombinant protein of the extracellular domain of Kell (CD238)

Recommended Dilutions

Western Blot 1:500-1:1000

Buffer

Lyophilized from a 0.2 µm filtered solution in PBS. Reconstitute the antibody with 200 µl sterile PBS (final concentration 0.5mg/ml).

Uses

This antibody detects mouse CD238 in Western blotting.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-22496

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

