

NBP1-80007**Advillin Antibody****Unit Size**

0.05 mg

Concentration

Lyoph

Storage

Store at -20C. Avoid freeze-thaw cycles.

Applications

WB

Species

Human, Mouse, Rat, Canine

Molecular Weight

92kDa

Host

Rabbit

Clonality

Polyclonal

Purity

Peptide affinity purified

Preservative

No Preservative

Immunogen

Synthetic peptide directed towards the middle region of human AVIL (NP_006567). Peptide sequence: PKYYPIAVLLKNQNQLPEDVNPAAKKENYLSEQDFVSVFGITRGQFAALP

Recommended Dilutions

Western Blot 0.2-1 ug/ml

Buffer

Lyophilized from PBS & 2% Sucrose. Centrifuge vial prior to reconstitution. Add 50 ul distilled water to a final antibody concentration of 1 mg/ml.

Uses

This is a rabbit polyclonal antibody against AVIL and was validated on Western blot.

ImagesWestern Blot: Advillin Antibody [NBP1-80007] -
Human Placenta lysate, concentration 0.2-1 ug/ml.

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit www.novusbio.com/guarantee.

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

