
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-18651

NBP1-18651

VEGF Receptor 3 Antibody (9D9)



Unit Size
0.1 mg

Concentration
lyoph

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, ELISA, IHC, IHC-P, IP

Species
Human

Host
Mouse

Clonality
Monoclonal

Isotype
IgG1

Purity
Protein A purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
Mouse Monoclonal to VEGFR-3 (#1)

Immunogen
Recombinant human soluble FLT-4 protein

Recommended Dilutions
ELISA 0.5-1.5 ug/ml, Western Blot 0.5-1 ug/ml, Immunoprecipitation 1-10 ug/ml, Immunohistochemistry, Immunohistochemistry-Paraffin

Buffer
Lyophilized. Add diH20 to desired concentration.

Uses
ELISA: To detect human VEGFR-3/FLT-4 by direct ELISA a concentration of 0.5 - 1.5 ug/ml can be used. This purified IgG, in combination with compatible secondary reagents, allows the detection of 0.25- 0.5 ng/well rhVEGFR-3/FLT-4. For Western blot analysis, the antibody can be used at 0.5 - 1 ug/ml with the appropriate secondary reagents to detect human VEGFR-3/FLT-4. Depending on the visualisation... See more at www.novusbio.com/NBP1-18651

Images
Western Blot: VEGF Receptor 3 Antibody (9D9) [NBP1-18651] - Analysis using recombinant human soluble VEGF Receptor 3 as target.



Notes
Clone #1 changed to 9D9 as a more unique identifier.

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com