

NBP1-77233**TEM8 Antibody****Unit Size**

0.1 mg

Concentration

1 mg/ml

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB, ELISA, ICC/IF, IHC, IHC-P

Species

Human, Mouse, Rat

Host

Rabbit

Clonality

Polyclonal

Purity

Ion exchange chromatography

Preservative

0.02% Sodium Azide

Specificity/Sensitivity

Recognizes all three isoforms of ATR.

Immunogen

Antibody was raised against a peptide corresponding to 13 amino acids near the center of human ATR (NP_444262).

Recommended Dilutions



ELISA, Immunocytochemistry/Immunofluorescence, Immunohistochemistry, Immunohistochemistry-Paraffin, Western Blot 0.5-1 ug/ml

Buffer

PBS

Uses

ATR antibody can be used for detection of ATR by Western blot at 0.5 to 1 mg/ml. It is human, mouse, and rat reactive. It will recognize all three isoforms.

ImagesWestern Blot: ATR Antibody [NBP1-77233] - HepG2 cell lysates with ATR antibody (IN) at (A) 0.5, (B) 1, and (C) 2 ug/ml. Immunohistochemistry-Paraffin: ATR Antibody [NBP1-77233] - Human brain tissue using ATR antibody at 2 ug/ml. 

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

