
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-57977

NBP1-57977

Surfactant Protein B Antibody



Unit Size
0.05 mg

Concentration
lyoph

Storage
Store at -20C. Avoid freeze-thaw cycles.

Applications
WB

Species
Human, Rat

Host
Rabbit

Clonality
Polyclonal

Purity
Peptide affinity purified

Preservative
No Preservative

Updated 3/9/2013 2.0


Immunogen
Synthetic peptides corresponding to SFTPB(surfactant, pulmonary-associated protein B) The peptide sequence was selected from the middle region of SFTPB. Peptide sequence PGALQARPGPHTQDLSEQQFPIPLPYCWLCRALIKRIQAMIPKGALAVAV.

Recommended Dilutions
Western Blot

Buffer
PBS & 2% Sucrose lyophilized with the antibody.Centrifuge the vial of lyoph antibody at 12,000 x g for 20 seconds. Add 50ul of distilled water. Vortex followed by centrifuge again to pellet the solution.Final concentration is 1 mg/ml in PBS buffer

Uses
This is a rabbit polyclonal antibody against SFTPB and was validated on Western blot.

Images
Western Blot: Surfactant Protein B Antibody [NBP1-57977] - Titration: 0.2-1 ug/ml, Positive Control: 721_B cell lysate.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com