

NBP1-50059**ZAP70 Antibody (1E7.2)****Unit Size**

0.1 mg

Concentration

1 mg/ml

Storage

Store at 4C. Do not freeze.

Applications

WB, FLOW, ICC/IF, IP

Species

Human, Mouse

Host

Mouse

Clonality

Monoclonal

Isotype

IgG1

Purity

IgG purified

Preservative

15mM Sodium Azide

Specificity/Sensitivity

The mouse monoclonal antibody 1E7.2 recognizes ZAP-70, a 70 kDa protein tyrosine kinase expressed in T and NK cells.

ZAP-70 is a molecule susceptible to degradation. It is recommended to use freshly prepared cell lysates (protease inhibitors are essential) to avoid non-specific staining of degradation products.

Immunogen

A KLH-coupled peptide corresponding to amino acids 282-307 of human ZAP-70

Recommended Dilutions

Flow Cytometry, Immunoprecipitation 1:50, Western Blot 1:1000, Immunocytochemistry/Immunofluorescence

Buffer

PBS, pH 7.4

Uses

This antibody is useful in Flow Cytometry, immunoprecipitation, Western Blot, Immunocytochemistry.

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-50059

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

