

NBP1-51121**CD14 Antibody (Sa14-2)****Unit Size**

0.05 mg

Concentration

Please see the vial label for concentration.

Storage

Store at 4°C. Do not freeze.

Applications

WB, FLOW

Species

Mouse

Host

Rat

Clonality

Monoclonal

Isotype

IgG2a

Purity

IgG purified

Preservative

No Preservative

Immunogen

The monoclonal antibody Sa14-2 reacts with the mouse monocyte marker CD14, a 53 kDa glycoprotein.

Recommended Dilutions

Flow Cytometry

Western Blot

Buffer


0.2 um filtered antibody solution in PBS, containing and 0.1% bovine serum albumin.

Uses


This product works in Flow Cytometry and Western Blot.

Images

Immunocytochemistry/Immunofluorescence: CD14 Antibody (Sa14-2) [NBP1-51121] - RAW264.7 cells were grown on coverslips, fixed with 1% paraformaldehyde and blocked with BSA. As primary antibody was used at 2 ug/ml in PBS/BSA 3%.



Flow Cytometry: CD14 Antibody (Sa14-2) [NBP1-51121] - 100000 RAW264.7 cells were stained with 1ug/ml antibody for 1h at 4°C (black - no staining; Red - isotype c ontrol; blue-NBP1-51121)



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

