
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-47427

NBP1-47427

Nanog Antibody (1E6C4)



Unit Size
0.1 ml

Concentration
This product is unpurified. The exact concentration of antibody is not quantifiable.

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, ELISA, ICC/IF

Species
Human

Molecular Weight
35kDa

Host
Mouse

Clonality
Monoclonal

Isotype
IgG1

Purity
Ascites

Preservative
0.03% Sodium Azide

Marker
Embryonic Stem Cell Marker

Updated 3/9/2013 2.0


Immunogen
Purified recombinant fragment of NANOG (aa20-166) expressed in E. Coli.

Recommended Dilutions
Western Blot 1: 500 - 1:2000, ELISA 1:10000, Immunocytochemistry/Immunofluorescence 1:200-1:1000


Buffer
Ascites

Uses
This antibody is useful in Immunofluorescence, Western Blot, and ELISA.

Images



Western Blot: NANOG Antibody (1E6C4) [NBP1-47427] - Western blot analysis using anti-NANOG monoclonal antibody against NTERA-2 cell lysate (2).



Immunofluorescence: NANOG Antibody (1E6C4) [NBP1-47427] - Confocal immunofluorescence analysis of NTERA-2 cells (left) and HeLa cells (right) using anti-Nanog Mouse mAb (green). Red: Actin filaments have been labeled with DY-554 phalloidin.

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com