

NBP1-18652**VEGF Receptor 3 Antibody (9D9) [Biotin]****Unit Size**

0.05 mg

Concentration

lyoph

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB, ELISA, IP

Species

Human

Host

Mouse

Clonality

Monoclonal

Conjugate

Biotin

Purity

Protein A purified

Preservative

No Preservative

Specificity/Sensitivity

Mouse Monoclonal to VEGFR-3 (#1)

Immunogen

Recombinant human soluble FLT-4 protein

Recommended Dilutions

ELISA 0.5-1.5 ug/ml

Western Blot 0.5-1 ug/ml

immunoprecipitation 1-5 ug/ml,

Buffer

Lyophilized. Add diH2O to desired concentration.

Uses

ELISA: To detect human VEGFR-3/FLT-4 by direct ELISA a concentration of 0.5 - 1.5 ug/ml can be used. This purified IgG, in combination with compatible secondary reagents, allows the detection of 0.25- 0.5 ng/well rhVEGFR-3/FLT-4. Western Blot: For Western blot analysis, the antibody can be used at 0.5 - 1 ug/ml with the appropriate secondary reagents to detect human VEGFR-3/FLT-4. Depending on the... See more at www.novusbio.com/NBP1-18652

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-18652

Notes

Clone #1 changed to 9D9 as a unique identifier.

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

