
NB300-263

Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB300-263

NB300-263

Ubiquitin Antibody



Unit Size
0.1 ml

Concentration
1.0 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB

Species
Human, Bovine

Host
Rabbit

Clonality
Polyclonal

Isotype
IgG

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide


Updated 3/9/2013 2.0

Immunogen
A synthetic peptide mapping to a region between between residues 1 and 50 of human Ubiquitin using the numbering given in Swiss-Prot entry P62988.

Recommended Dilutions
Western Blot 1:1000 - 1:10000

Buffer
Tris-citrate/phosphate buffer, pH 7 to 8

Images



Western Blot: Ubiquitin Antibody [NB300-263] - Detection of Ubiquitin by Western Blotting of Products from an Ubiquitination Assay and Purified Ubiquitin. Samples: A) Ubiquitination assay was performed as described in Zhang et al., 2004, M... See more at www.novusbio.com/NB300-263

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com