

NB300-675B**UCHL1 Antibody [Biotin]****Unit Size**

0.1 ml

Concentration

1.0 mg/ml

Storage

Store at 4C in the dark.

Applications

WB, IHC

Species

Human, Mouse, Rat, Bovine, Equine, Guinea Pig, Primate, Porcine

Host

Rabbit

Clonality

Polyclonal

Conjugate

Biotin

Purity

Affinity purified

Preservative

No Preservative

Marker

Neuronal Marker

Specificity/Sensitivity

Rabbit Polyclonal to PGP9.5 - Peripheral Nerve Fiber marker

Immunogen

A synthetic peptide made to an internal portion of the human UCHL1 protein sequence (between residues 100-200). UniProt P09936

Recommended Dilutions

immunohistochemistry 2.5-5.0 ug/ml, Western Blot 0.5-2.0 ug/ml,

Buffer

PBS

Uses

This antibody is useful for Western blot and immunohistochemistry. By Western blot a band at ~25 kDa is seen.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB300-675B

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit www.novusbio.com/guarantee.

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

