

NB500-169G**BrdU Antibody (BU1/75 (ICR1)) [DyLight 488]****Unit Size**

0.1 mg

Concentration

1.0 mg/ml

Storage

Store at 4°C in the dark.

Applications

FLOW, ICC/IF, IHC, IHC-P

Species

All Species

Host

Rat

Clonality

Monoclonal

Isotype

IgG2a

Conjugate

DyLight 488

Purity

IgG purified

Preservative

No Preservative

Marker

Proliferation Marker

Specificity/Sensitivity

This reacts with BrdU in single stranded DNA, BrdU attached to a protein carrier or free BrdU. It detects nucleated cells in S-Phase which have had BrdU incorporated into their DNA. Also reacts with chlorodeoxyuridine but with reduced staining.

Immunogen

Made to Chemical BrdU

Recommended Dilutions

Flow Cytometry 1:25 - 1:200, Immunohistochemistry-Paraffin, Immunocytochemistry/Immunofluorescence, Immunohistochemistry

Buffer

50mM Sodium Borate

Uses

Optimal dilutions/concentrations should be determined by the end user.

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB500-169G

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

