
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB110-89453

NB110-89453

BLK Antibody (9D10A8F8)



Unit Size
0.1 ml

Concentration
This product is unpurified. The exact concentration of antibody is not quantifiable.

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, ELISA, IHC, IHC-Fr, IHC-P

Species
Human

Host
Mouse

Clonality
Monoclonal

Purity
Ascites

Preservative
0.03% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
BLK (9D10A8F8)

Immunogen
Ni-NTA purified truncated recombinant BLK expressed in E. Coli strain BL21 (DE3)

Recommended Dilutions
ELISA 1:10000, Western Blot 1:500-1:2000, Immunohistochemistry-Paraffin 1:500-1:2000, Immunohistochemistry-Frozen 1:500-1:2000, Immunohistochemistry

Uses
This antibody is useful in Western Blot, IHC(P),IHC(F), and ELISA.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB110-89453

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com