

NB120-2736**Nucleoporin p62 Antibody (RL31)****Unit Size**

0.2 ml

Concentration

Concentrations vary lot to lot. See vial label for concentration.

Storage

Store at 4°C short term. Aliquot and store at -20°C long term. Avoid freeze-thaw cycles.

Applications

WB, ICC/IF

Species

Rat

Host

Armenian Hamster

Clonality

Monoclonal

Isotype

IgG

Purity

IgG purified

Preservative

0.05% Sodium Azide

Specificity/Sensitivity

Detects the nucleoporin p62 O-linked glycoprotein in the p62 complex from rat tissues.

Immunogen

O-linked glycoprotein-enriched fraction from rat liver nuclear envelopes.

Recommended Dilutions

Immunocytochemistry/Immunofluorescence 1:50

Western Blot 1:200

Buffer

PBS

Uses

This antibody detects a single 62 kDa protein representing nucleoporin p62 in rat liver nuclear envelope fractions. Immunofluorescence staining of p62 in rat liver with this antibody results in staining of both the nucleoplasmic and cytoplasmic surfaces of the nuclear pore complex (NPC).

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB120-2736

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

