
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-93306

## NB100-93306

# eIF3X Antibody



### Unit Size
0.1 ml

### Concentration
0.2 mg/ml

### Storage
Store at 4C. Do not freeze.

### Applications
WB, IP

### Species
Human

### Host
Rabbit

### Clonality
Polyclonal

### Purity
Immunogen affinity purified

### Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0


## Immunogen
The immunogen recognized by this antibody maps to a region between residue 1259 and 1309 of human putative eukaryotic translation initiation factor 3 subunit using the numbering given in entry NP_056044.3 (GeneID 23277).

## Recommended Dilutions
Immunoprecipitation 2-5 mcg/mg lysate, Western Blot 1:2000-1:10000

## Buffer
Tris-buffered Saline and 0.1% BSA

## Uses
This antibody is useful for western blot and immunoprecipitation.

## Images
Western Blot: eIF3X Antibody [NB100-93306] - Samples: Whole cell lysate from HeLa (5, 15 and 50 mcg for WB; 1 mg for IP, 20% of IP loaded) and 293T (T; 50 mcg) cells. Antibody: Affinity purified rabbit anti-eIF3X antibody NB100-93306 used f... See more at www.novusbio.com/NB100-93306



*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months.* ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

**Novus USA**
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

**Novus Canada**
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

**Novus Europe**
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com