

NB100-61054**TFII-I Antibody****Unit Size**

0.1 ml

Concentration

0.2 mg/ml

Storage

Store at 4C. Do not freeze.

Applications

WB, ICC/IF, IHC, IHC-P, IP

Species

Human, Mouse

Host

Rabbit

Clonality

Polyclonal

Purity

Immunogen affinity purified

Preservative

0.09% Sodium Azide

Immunogen

The immunogen recognized by this antibody maps to a region between residue 985 and 998 of human general transcription factor II, i using the numbering given in entry NP_127492.1 (GeneID 2969).

Recommended Dilutions

Immunocytochemistry/Immunofluorescence, Immunohistochemistry, Immunohistochemistry-Paraffin 1:100 - 1:500, Immunoprecipitation 2-5 ug/mg lysate, Western Blot 1:2000-1:10000

Buffer


Tris-buffered Saline and 0.1% BSA

Uses


This antibody is useful for Western Blot and Immunoprecipitation

Images (more available at www.novusbio.com/NB100-61054)

Immunocytochemistry/Immunofluorescence: TFII-I Antibody [NB100-61054] - FFPE section of human colon carcinoma. Affinity purified rabbit anti-GTF2I/TF II-I used at a dilution of 1:100.



Immunohistochemistry-Paraffin: TFII-I Antibody [NB100-61054] - Human Ewing sarcoma (left) and mouse teratoma (right). Antibody used at a dilution of 1:200.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

