

NB100-2521H**Speedy/Ringo Antibody [HRP]****Unit Size**

0.1 ml

Concentration

1.1 mg/ml

Storage

Store at 4C in the dark.

Applications

WB

Species

Mouse

Host

Rabbit

Clonality

Polyclonal

Conjugate

HRP

Purity

Affinity purified

Preservative

No Preservative

Specificity/Sensitivity

This is specific for Speedy/Ringo protein.

Immunogen

A synthetic peptide made to a C-terminal region of the human Speedy protein (within residues 200-286). This immunogen is conserved in both isoforms 1 and 2. [Swiss-Prot Q5MJ69]

Recommended Dilutions

Western Blot

Buffer

PBS

Uses

This antibody is useful for Western blot analysis, where a band is seen at ~36 kDa (isoform 2). After a longer exposure, a 31 kDa band can be detected (isoform 1). There is also a non-specific band at ~58 kDa. This antibody was tested against human and mouse brain samples, but failed to detect proteins of the predicted size in either lysate.

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-2521H

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

