9F, No. 108, Jhouzih St.,Taipei, Taiwan
Tel: + 886-2-8751-1888 Fax: + 886-2-6602-1218
E-mail: sales@abnova.com

Datasheet

APOF MaxPab mouse polyclonal antibody (B01)

Catalog Number: H00000319-B01

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a full-length human APOF protein.

Immunogen: APOF (AAH26257, 37 a.a. ~ 327 a.a) full-length human protein.

Sequence:
TSYGKQTNVLMHFPLSLESQTPSSDPLSCQFLHPKSL
PGFSHMAPLPKFLVSLALRNDALEEAGCQADVWALQL
QLYRQGGVNATQVLIQHLRGLQKGRSTERNVSVEALA
SALQLLAREQQSTGRVGRSLPTEDCENEKEQAVHNV
VQLLPGVGTFYNLGTALYYATQNCLGKARERGRDGAI
DLGYDLLMTMAGMSGGPMGLAISAALKPALRSGVQQL
IQYYQDQKDANISQPETTKEGLRAISDVSDLEETTTLAS
FISEVVSSAPYWGWAIIKSYDLDPGAGSLEI

Host: Mouse

Reactivity: Human

Applications: Det Ab, WB-Tr
(See our web site product page for detailed applications information)

Protocols: See our web site at http://www.abnova.com/support/protocols.asp or product page for detailed protocols

Storage Buffer: No additive

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 319

Gene Symbol: APOF

Gene Alias: Apo-F, DKFZp781G18150, LTIP, MGC22520

Gene Summary: The product of this gene is one of the minor apolipoproteins found in plasma. This protein forms complexes with lipoproteins and may be involved in transport and/or esterification of cholesterol. [provided by RefSeq]