

Datasheet

MFGE8 monoclonal antibody, clone MFG-06

Catalog Number: MAB3634

Regulatory Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody raised against native MFGE8.

Clone Name: MFG-06

Immunogen: Native purified human MFGE8.

Host: Mouse

Theoretical MW (kDa): 40-45

Reactivity: Human

Applications: IHC-P, WB

(See our web site product page for detailed applications information)

Protocols: See our web site at <http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Specificity: This antibody reacts with 40-45 KDa glycoprotein in human milk fat globulemembrane preparation.

Form: Liquid

Isotype: IgG1

Recommend Usage: The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS, pH 7.4 (0.09% sodium azide)

Storage Instruction: Store at 4°C. Do not freeze. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 4240

Gene Symbol: MFGE8

Gene Alias: BA46, EDIL1, HsT19888, OAcGD3S, SED1, SPAG10, hP47

References:

1. The histone deacetylase inhibitor suberoylanilide hydroxamic acid induces differentiation of human breast cancer cells. Munster PN, Troso-Sandoval T, Rosen N, Rifkind R, Marks PA, Richon VM. Cancer Res. 2001 Dec 1;61(23):8492-7.
2. Differentiation patterns of testicular germ-cell tumours as revealed by a panel of monoclonal antibodies. Bartkova J, Rejthar A, Bartek J, Kovarik J. Tumour Biol. 1987;8(1):45-56.