

Datasheet

MLC1SA MaxPab mouse polyclonal antibody (B01)

[provided by RefSeq]

Catalog Number: H00140465-B01

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a full-length human MLC1SA protein.

Immunogen: MLC1SA (NP_002466, 1 a.a. ~ 208 a.a) full-length human protein.

Sequence:

MPPKKDVPVKKPAGPSISKPAAKPAAAGAPPAKTAE
PAVPQAPQKTQEPPVDLSKVVEFNKDQLEEFKEAFEL
FDRVGDGKILYSQCGDVMRALGQNPTNAEVLKVLGNP
KSDELKSRRVDFETFLPMLQAVAKNRGQGTIEDYLEG
FRVFDKEGNGKVMGAELRHVLTTLGEKMTEEEVETVL
AGHEDSNGCINYEAFKHLISV

Host: Mouse

Reactivity: Human

Applications: WB-Tr

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: No additive

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 140465

Gene Symbol: MYL6B

Gene Alias: MLC1SA

Gene Summary: Myosin is a hexameric ATPase cellular motor protein. It is composed of two heavy chains, two nonphosphorylatable alkali light chains, and two phosphorylatable regulatory light chains. This gene encodes a myosin alkali light chain expressed in both slow-twitch skeletal muscle and in nonmuscle tissue.