9F, No. 108, Jhouzih St.,Taipei, Taiwan
Tel: + 886-2-8751-1888 Fax: + 886-2-6602-1218
E-mail: sales@abnova.com

Datasheet

LONRF2 MaxPab mouse polyclonal antibody (B01)

Catalog Number: H00164832-B01

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a full-length human LONRF2 protein.

Immunogen: LONRF2 (AAI01665.1, 1 a.a. ~ 511 a.a) full-length human protein.

Sequence:
MKNYEQALQDASAACQNEPLLIKGHQVKAQALSGLGR
SKEVLKEFLYCLALNPECNSVKKEAQKVMCEVLFSATA
NVHENLTSSIQSRLKAQGHSHMNAQALLEEGDAGSSE
NSSEKSDMLGNTNSSVLYFILGLHFEEDKKALESILPTA
PSAGLKRQFPDDVEDAPDLNAPGKIPKKDLSPQRSPN
SETEESQGLSLDVTDFECALCMRLLFEPVTTPCGHTF
CLKCLERCLDHAPHCPLCKDKLSELLASRNFNITVLAE
ELIFRYLPDELSDRKRIYDEEMSELSNLTRDVPIFVCAM
AFPTVPCPLHVFEPRYRLMIRRCMETGTKRFGMCLSA
EHAGLSEYGCMLEIKDVRTFPDGSSVVDAIGISRFRVL
SHRHRDGYNTADIEYLEDEKVEGPEYEELAALHDSVH
QQSVSWFASLQDRMKEQILSHFGVMPDREPEPQSNP
SGPAWSWWILAVLPLERKAQLAILGMTSLKERLLAIRRI
LVIITRKMNSRQELANARERNN

Host: Mouse

Reactivity: Human

Applications: WB-Tr
(See our web site product page for detailed applications information)

Protocols: See our web site at http://www.abnova.com/support/protocols.asp or product page for detailed protocols

Storage Buffer: No additive

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 164832

Gene Symbol: LONRF2

Gene Alias: FLJ45273, MGC126711, MGC126713, RNF192