

Datasheet

CD300A purified MaxPab mouse polyclonal antibody (B02P)

Catalog Number: H00011314-B02P

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a full-length human CD300A protein.

Immunogen: CD300A (NP_009192.2, 1 a.a. ~ 299 a.a) full-length human protein.

Sequence:

MWLPWALLLLWVPGCFALSKCRTVAGPVGGSLSVQC
PYEKEHRTL NKYWCRPPQIFLCDKIVETKGSAGKRNG
RVSIRDSPANLSFTVTLENLTEEDAGTYWCGVDPWL
RDFHDPVVEVEVSVPASTSMTPASITA AKTSTITTAFP
PVSTTLFAVGATHSASIQEETEEVNSQLPLLLSLLAL
LLLLLVGASLLAWRMFQKWIKAGDHSELSQNPQAAT
QSELHYANLELLMWPLQEKPAPPREVEVEYSTVASPR
EELHYASVVFDSENTNRIAAQRPREEEPDSYSVIRKT

Host: Mouse

Reactivity: Human

Applications: WB-Tr

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 11314

Gene Symbol: CD300A

Gene Alias: CMRF-35-H9, CMRF-35H, CMRF35H, CMRF35H9, IGSF12, IRC1, IRC2, IRp60

Gene Summary: The CMRF35 antigen (CMRF35A; MIM 606786), which was identified by reactivity with a monoclonal antibody, is present on monocytes,

neutrophils, and some T and B lymphocytes. CMRF35H is recognized by the same antibody and is distinct from CMRF35 (Green et al., 1998 [PubMed 9701027]).[supplied by OMIM]