

Datasheet

FLVCR1 polyclonal antibody

Catalog Number: PAB6710

Regulation Status: For research use only (RUO)

Product Description: Goat polyclonal antibody raised against synthetic peptide of FLVCR1.

Immunogen: A synthetic peptide corresponding to human FLVCR1.

Sequence: C-KTVMLSKQSESAI

Host: Goat

Theoretical MW (kDa): 59.9

Reactivity: Human

Applications: ELISA, WB-Ti

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Form: Liquid

Purification: Antigen affinity purification

Concentration: 0.5 mg/mL

Recommend Usage: ELISA (1:128000)

Western Blot (0.1-0.3 ug/mL)

The optimal working dilution should be determined by the end user.

Storage Buffer: In Tris saline, pH 7.3 (0.5% BSA, 0.02% sodium azide)

Storage Instruction: Store at -20°C.

Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 28982

Gene Symbol: FLVCR1

Gene Alias: FLVCR

References:

1. Enhanced alternative splicing of the FLVCR1 gene in Diamond Blackfan anemia disrupts FLVCR1 expression and function that are critical for erythropoiesis. Rey MA, Duffy SP, Brown JK, Kennedy JA, Dick JE, Dror Y, Taylor CS. Haematologica. 2008 Nov;93(11):1617-26. Epub 2008 Sep 24.