

## Datasheet

### RB1 monoclonal antibody, clone 7F12

**Catalog Number:** MAB2165

**Regulation Status:** For research use only (RUO)

**Product Description:** Mouse monoclonal antibody raised against partial recombinant RB1.

**Clone Name:** 7F12

**Immunogen:** Recombinant protein corresponding to amino acids 280-330 of RB1.

**Host:** Mouse

**Reactivity:** Human

**Applications:** ELISA, IP, WB

(See our web site product page for detailed applications information)

**Protocols:** See our web site at <http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

**Specificity:** This antibody recognizes an epitope within aa 280-330 of RB1.

**Form:** Liquid

**Isotype:** IgG1

**Recommend Usage:** The optimal working dilution should be determined by the end user.

**Storage Buffer:** In PBS, pH 7.4

**Storage Instruction:** Store at -20°C.  
Aliquot to avoid repeated freezing and thawing.

**Entrez GeneID:** 5925

**Gene Symbol:** RB1

**Gene Alias:** OSRC, RB, p105-Rb, pRb, pp110

**Gene Summary:** The protein encoded by this gene is a negative regulator of the cell cycle and was the first

tumor suppressor gene found. The encoded protein also stabilizes constitutive heterochromatin to maintain the overall chromatin structure. The active, hypophosphorylated form of the protein binds transcription factor E2F1. Defects in this gene are a cause of childhood cancer retinoblastoma (RB), bladder cancer, and osteogenic sarcoma. [provided by RefSeq]

#### References:

1. Retinoblastoma protein monoclonal antibodies with novel characteristics. Wen SF, Nodelman M, Nared-Hood K, Duncan J, Geradts J, Shepard HM. J Immunol Methods. 1994 Mar 10;169(2):231-40.