

Datasheet

NLRX1 polyclonal antibody

Catalog Number: PAB19300

Regulation Status: For research use only (RUO)

Product Description: Rabbit polyclonal antibody raised against synthetic peptide of NLRX1.

Immunogen: A synthetic peptide corresponding to 14 amino acids near N-terminus of human NLRX1.

Host: Rabbit

Reactivity: Human, Mouse, Rat

Applications: ELISA, IHC, WB-Ti
(See our web site product page for detailed applications information)

Protocols: See our web site at
<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Form: Liquid

Purification: Peptide affinity purification

Concentration: 1 mg/mL

Recommend Usage: Western Blot (1-2 ug/mL)
Immunohistochemistry (10 ug/mL)
The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS (0.02% sodium azide)

Storage Instruction: Store at 4°C for three months. For long term storage store at -20°C.
Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 79671

Gene Symbol: NLRX1

Gene Alias: CLR11.3, DLNB26, FLJ21478,
MGC131937, MGC21025, NOD26, NOD5, NOD9

Gene Summary: This gene encodes a member of the NLR family. Alternative splicing has been observed at

this gene locus and two transcript variants, encoding distinct isoforms, have been identified. [provided by RefSeq]