

Datasheet

LARP2 polyclonal antibody

Catalog Number: PAB22975

Regulation Status: For research use only (RUO)

Product Description: Rabbit polyclonal antibody raised against recombinant LARP2.

Immunogen: Recombinant protein corresponding to amino acids of human LARP2.

Sequence:

KHKWVPLHLDVVRSESQERPGSRNSSRCQPEANKPT
HNNRRNDTRSWKRDREKRDDQDDVSSVRSEGGNIR
GSF

Host: Rabbit

Reactivity: Human

Applications: IHC-P

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Form: Liquid

Purification: Antigen affinity purification

Isotype: IgG

Recommend Usage: Immunohistochemistry

(1:50-1:200)

Western Blot (1:250-1:500)

The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)

Storage Instruction: Store at 4°C. For long term storage store at -20°C.

Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 55132

Gene Symbol: LARP2

Gene Alias: DKFZp686L13217, MGC117277, MGC75174

Gene Summary: This gene encodes a protein containing domains found in the La related protein of *Drosophila melanogaster*. La motif-containing proteins are thought to be RNA-binding proteins, where the La motif and adjacent amino acids fold into an RNA recognition motif. The La motif is also found in proteins unrelated to the La protein. Alternative splicing has been observed at this locus and three variants, encoding distinct isoforms, are described. Additional splice variation has been identified but the full-length nature of these transcripts has not been determined. [provided by RefSeq]