

Datasheet

WBP4 polyclonal antibody

Catalog Number: PAB23372

Regulation Status: For research use only (RUO)

Product Description: Rabbit polyclonal antibody raised against recombinant WBP4.

Immunogen: Recombinant protein corresponding to amino acids of human WBP4.

Sequence:

YCKCWIADNRPSVEFHERGKNHKNVAKRISEIKQKSL
DKAKEEEKASKEFAAMEAAALKAYQEDLKRLGLESEIL
EPSITPVTSTIPTSTSNQQKEK

Host: Rabbit

Reactivity: Human

Applications: IF, IHC-P

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Form: Liquid

Purification: Antigen affinity purification

Isotype: IgG

Recommend Usage: Immunohistochemistry

(1:200-1:500)

Western Blot (1:250-1:500)

Immunofluorescence (1-4 ug/mL)

The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)

Storage Instruction: Store at 4°C. For long term storage store at -20°C.

Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 11193

Gene Symbol: WBP4

Gene Alias: FBP21, MGC117310

Gene Summary: This gene encodes WW domain-containing binding protein 4. The WW domain represents a small and compact globular structure that interacts with proline-rich ligands. This encoded protein is a general spliceosomal protein that may play a role in cross-intron bridging of U1 and U2 snRNPs in the spliceosomal complex A. [provided by RefSeq]