
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBL1-08142

## NBL1-08142

# C12orf43 Overexpression Lysate



## Unit Size
0.1 mg

## Storage
Store at -80C. Avoid freeze-thaw cycles.

## Applications
WB

## Molecular Weight
28kDa

## Purity
Protein

Updated 3/9/2013 2.0

## Specificity/Sensitivity
Homo sapiens chromosome 12 open reading frame 43 (C12orf43), mRNA.


## Immunogen
The lysate was created in HEK293T cells, using plasmid ID RC204834 and based on accession number NM_022895. The protein contains a C-terminal DDK tag.

## Recommended Dilutions
Western Blot

## Buffer
RIPA buffer

## Uses
This product is intended for use as a positive control in Western Blot. You will receive the lysate (100ug), and an empty vector negative control (100 ug).

## Images
Western Blot: C12orf43 Overexpression Lysate (Adult Normal) [NBL1-08142] Left-Empty vector transfected control cell lysate (HEK293 cell lysate); Right -Over-expression Lysate for C12orf43.



## Notes
This product is manufactured by and sold under license from OriGene Technologies and its use is limited solely for research purposes. Please note that “1 mg/ml” refers to the total protein concentration and that the specific protein concentration is not determined at this time.

*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months.* ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

**Novus USA**
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

**Novus Canada**
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

**Novus Europe**
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com