



MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Date of issue: 02/04/2013

Version 1.0

SECTION 1. Identification

Product identifier

Product number	820928
Product name	1-Octene for synthesis

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Chemical for synthesis
-----------------	------------------------

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821, United States of America SDS Phone Support: +1-978-715-1335 General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5) e-mail: mm_sds@merckgroup.com
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

SECTION 2. Hazards identification

GHS Classification

Flammable liquid, Category 2, H225
Skin irritation, Category 2, H315
Eye irritation, Category 2, H319
Aspiration hazard, Category 1, H304
Chronic aquatic toxicity, Category 2, H411

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word
Danger

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 820928
Product name 1-Octene for synthesis

Version 1.0

Hazard Statements

H225 Highly flammable liquid and vapor.
H304 May be fatal if swallowed and enters airways.
H315 Causes skin irritation.
H319 Causes serious eye irritation.
H411 Toxic to aquatic life with long lasting effects.

Precautionary Statements

P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
P240 Ground/bond container and receiving equipment.
P273 Avoid release to the environment.
P301 + P310 IF SWALLOWED: Immediately call a POISON CENTER or doctor/ physician.
P331 Do NOT induce vomiting.
P302 + P352 IF ON SKIN: Wash with plenty of soap and water.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula	$\text{CH}_3(\text{CH}_2)_5\text{CH}=\text{CH}_2$	C_8H_{16} (Hill)
CAS-No.	111-66-0	
Molar mass	112.21 g/mol	

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

Oct-1-ene (>= 90 % - <= 100 %)

111-66-0

2-ethylhex-1-ene (>= 1 % - < 5 %)

1632-16-2

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eye contact

After eye contact: rinse out with plenty of water. Call in ophthalmologist.

Ingestion

After swallowing: caution if victim vomits. Risk of aspiration! Keep airways free. Pulmonary failure possible after aspiration of vomit. Call a physician immediately.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 820928
Product name 1-Octene for synthesis

Version 1.0

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

irritant effects, Dermatitis, Gastrointestinal disturbance, Headache, Unconsciousness, Irregular cardiac activity, narcosis, Lung edema
Drying-out effect resulting in rough and chapped skin.

Indication of any immediate medical attention and special treatment needed

Subsequently administer: activated charcoal (20 - 40 g in 10% slurry). Sodium sulfate (1 tablespoon/1/4 l water).

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Carbon dioxide (CO₂), Foam, Dry powder

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible.

Vapors are heavier than air and may spread along floors.

Forms explosive mixtures with air at ambient temperatures.

Pay attention to flashback.

Development of hazardous combustion gases or vapors possible in the event of fire.

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Cool closed containers exposed to fire with water spray. Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid substance contact. Do not breathe vapors, aerosols. Ensure adequate ventilation. Keep away from heat and sources of ignition. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains. Risk of explosion.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent material (e.g. Chemisorb®). Dispose of properly. Clean up affected area.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 820928
Product name 1-Octene for synthesis

Version 1.0

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Advice on protection against fire and explosion

Keep away from open flames, hot surfaces and sources of ignition. Take precautionary measures against static discharge.

Conditions for safe storage, including any incompatibilities

Keep container tightly closed in a dry and well-ventilated place. Keep away from heat and sources of ignition.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

Flame retardant antistatic protective clothing

Respiratory protection

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	liquid
Color	colorless

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	820928	Version 1.0
Product name	1-Octene for synthesis	

Odor	benzine-like
Odor Threshold	No information available.
pH	No information available.
Melting point	-102 °C
Boiling point	No information available.
Flash point	46 °F (8 °C) Method: c.c.
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	0.7 %(V)
Upper explosion limit	6.8 %(V)
Vapor pressure	17.3 hPa at 68 °F (20 °C)
Relative vapor density	3.9
Relative density	0.72 g/cm ³ at 68 °F (20 °C)
Water solubility	at 68 °F (20 °C) practically insoluble
Partition coefficient: n-octanol/water	log Pow: 4.57 (25 °C) (experimental) (IUCLID) Potential bioaccumulation
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.
Explosive properties	No information available.
Ignition temperature	430 °F (221 °C)
Viscosity, kinematic	0.38 mm ² /s at 104 °F (40 °C)

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 820928
Product name 1-Octene for synthesis

Version 1.0

SECTION 10. Stability and reactivity

Reactivity

Vapors may form explosive mixture with air.

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions

Violent reactions possible with:

Strong oxidizing agents, Strong acids, nitrates, chlorates, Peroxides

Conditions to avoid

Warming.

A range from approx. 15 Kelvin below the flash point is to be rated as critical.

Incompatible materials

no information available

Hazardous decomposition products

no information available

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Inhalation, Eye contact, Skin contact

Acute oral toxicity

LD50 rat: > 5,000 mg/kg (IUCLID)

Symptoms: Gastrointestinal disturbance

Acute inhalation toxicity

LC50 rat: 37.6 mg/l; 4 h (IUCLID)

Symptoms: Possible damages:, mucosal irritations, Lung edema

Acute dermal toxicity

LD50 rabbit: > 2,000 mg/kg
(IUCLID)

Skin irritation

rabbit

Result: Irritations
(IUCLID)

Drying-out effect resulting in rough and chapped skin. Dermatitis
Causes skin irritation.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 820928
Product name 1-Octene for synthesis

Version 1.0

Eye irritation

rabbit

Result: slight irritation
(IUCLID)

Causes serious eye irritation.

Sensitization

Sensitization test: guinea pig

Result: negative

Method: OECD Test Guideline 406

Genotoxicity in vitro

Ames test

Result: negative
(IUCLID)

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Aspiration hazard, Aspiration may cause pulmonary edema and pneumonitis.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

Systemic effects:

Headache, Unconsciousness, Cardiac irregularities, narcosis

Further data:

Other dangerous properties can not be excluded.

Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 820928
Product name 1-Octene for synthesis

Version 1.0

Toxicity to fish

LC50 Danio rerio (zebra fish): 4.8 mg/l; 96 h (External MSDS)

Toxicity to daphnia and other aquatic invertebrates

EC50 Daphnia magna (Water flea): 3.2 - 10 mg/l; 24 h (Lit.)

Persistence and degradability

No information available.

Bioaccumulative potential

Partition coefficient: n-octanol/water

log Pow: 4.57 (25 °C)

(experimental)

(IUCLID) Potential bioaccumulation

Mobility in soil

No information available.

Other adverse effects

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

UN number	UN 3295
Proper shipping name	HYDROCARBONS, LIQUID, N.O.S.
Class	3
Packing group	II
Environmentally hazardous	--

Air transport (IATA)

UN number	UN 3295
Proper shipping name	HYDROCARBONS, LIQUID, N.O.S.
Class	3
Packing group	II
Environmentally hazardous	--
Special precautions for user	no

Sea transport (IMDG)

UN number	UN 3295
Proper shipping name	HYDROCARBONS, LIQUID, N.O.S.
Class	3
Packing group	II
Environmentally hazardous	--
Special precautions for user	yes

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 820928
Product name 1-Octene for synthesis

Version 1.0

EmS

F-E S-D

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Flammable Liquid

Skin irritant

Eye irritant

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Fire Hazard

Acute Health Hazard

SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

Massachusetts Right To Know

Ingredients

Oct-1-ene

Pennsylvania Right To Know

Ingredients

Oct-1-ene

New Jersey Right To Know

Ingredients

Oct-1-ene

2-ethylhex-1-ene

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 820928
Product name 1-Octene for synthesis

Version 1.0

Notification status

TSCA: On TSCA Inventory

DSL: This product contains one or several components listed in the Canadian NDSL.
Ingredients
2-ethylhex-1-ene

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H225	Highly flammable liquid and vapor.
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H319	Causes serious eye irritation.
H411	Toxic to aquatic life with long lasting effects.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Date of issue:02/04/2013

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.