

**NB600-372****T7 Epitope Tag Antibody****Unit Size**

0.1 mg

**Concentration**

1.0 mg/ml

**Storage**

Store at 4°C. Do not freeze.

**Applications**

WB, ELISA, ICC/IF, IP

**Species**

Non-species specific

**Host**

Rabbit

**Clonality**

Polyclonal

**Purity**

Immunogen affinity purified

**Preservative**

0.09% Sodium Azide

**Immunogen**

Rabbits were immunized with T7 cleavage site (MASMTGGQQMG) conjugated to KLH. Antibody was isolated by affinity chromatography using the peptide immobilized on solid support. Rabbit anti-human T7 affinity purified antibodies were coupled to peptide immobilized on solid support.

**Recommended Dilutions**

ELISA Primary: 1:1,000 - 1:30,000; Coating: 1:100 - 1:500

Immunocytochemistry/Immunofluorescence 1:100- 1:400

Immunoprecipitation 1 - 4 ug/mg lysate

Western Blot 1:1000-1:30000

**Buffer**

Phosphate Buffered Saline (PBS)

**Uses**

ELISA, Western blot and immunocytochemistry.

**Images**

Western Blot: T7 Epitope Tag Antibody [NB600-372]  
 - 200, 100, or 50 ng of E. coli whole cell lysate  
 expressing a multi-tag fusion protein. Antibody used  
 at 0.04 ug/ml (1:25,000).

