



MATERIAL SAFETY DATA SHEET

according to the Global Harmonized System

Date of issue: 02/04/2013

Version 1.0

SECTION 1. Identification

Product identifier

Product number 820356
Product name Methyl cyanoacetate for synthesis

Relevant identified uses of the substance or mixture and uses advised against

Identified uses Chemical for synthesis

Details of the supplier of the safety data sheet

Company EMD Millipore Corporation | 290 Concord Road, Billerica, MA 01821,
United States of America | SDS Phone Support: +1-978-715-1335 |
General Inquiries: +1-978-751-4321 | Monday to Friday, 9:00 AM to
4:00 PM Eastern Time (GMT-5)

e-mail: mm_sds@merckgroup.com

Emergency telephone 613-996-6666 CANUTEC (Canada)
+1-703-527-3887 CHEMTREC (International)
24 Hours/day; 7 Days/week

SECTION 2. Hazards identification

GHS-Labeling

Precautionary Statements

P262 Do not get in eyes, on skin, or on clothing.

Not a hazardous substance or mixture according to Regulation (EC) No 1272/2008.

Other hazards

None known.

The following percentage of the mixture consists of ingredient(s) with unknown acute toxicity: 100 %

SECTION 3. Composition/information on ingredients

Formula	NCCH ₂ COOCH ₃	C ₄ H ₅ NO ₂ (Hill)
CAS-No.	105-34-0	
Molar mass	99.09 g/mol	

MATERIAL SAFETY DATA SHEET
according to the Global Harmonized System

Product number 820356
Product name Methyl cyanoacetate for synthesis

Version 1.0

Remarks WHMIS hazardous composition: No ingredients are hazardous according to the CPR criteria.

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eye contact

After eye contact: rinse out with plenty of water with the eyelid held wide open. Call in ophthalmologist if necessary.

Ingestion

After swallowing: make victim drink water (two glasses at most). Consult doctor if feeling unwell.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

The following applies to cyanogen compounds/ nitriles in general: utmost caution! Release of hydrocyanic acid is possible - blockade of cellular respiration. Cardiovascular disorders, dyspnoea, unconsciousness.

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Water, Carbon dioxide (CO₂), Foam, Dry powder

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible material, Vapors are heavier than air and may spread along floors.

Development of hazardous combustion gases or vapors possible in the event of fire., Fire may cause evolution of: Hydrogen cyanide (hydrocyanic acid)
nitrogen oxides

Forms explosive mixtures with air on intense heating.

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

MATERIAL SAFETY DATA SHEET
according to the Global Harmonized System

Product number 820356
Product name Methyl cyanoacetate for synthesis

Version 1.0

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid substance contact. Do not breathe vapors, aerosols. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent material (e.g. Chemizorb®). Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Protected from light. Tightly closed.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Change contaminated clothing. Wash hands after working with substance.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Respiratory protection

required when vapors/aerosols are generated.

MATERIAL SAFETY DATA SHEET
according to the Global Harmonized System

Product number 820356
Product name Methyl cyanoacetate for synthesis

Version 1.0

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	liquid
Color	colorless
Odor	aromatic
Odor Threshold	No information available.
pH	No information available.
Melting point	-22.5 °C
Boiling point/boiling range	397 °F (203 °C) at 1,013 hPa
Flash point	230 °F (110 °C) Method: c.c.
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapor pressure	0.13 hPa at 68 °F (20 °C)
Relative vapor density	No information available.
Relative density	1.13 g/cm ³ at 68 °F (20 °C)
Water solubility	54 g/l at 68 °F (20 °C)
Partition coefficient: n-octanol/water	log Pow: -0.47 (experimental) Bioaccumulation is not expected (log Pow <1).
Autoignition temperature	No information available.
Decomposition temperature	No information available.

MATERIAL SAFETY DATA SHEET
according to the Global Harmonized System

Product number 820356
Product name Methyl cyanoacetate for synthesis

Version 1.0

Viscosity, dynamic 3.0 mPa.s
at 68 °F (20 °C)

Explosive properties No information available.

Ignition temperature 892 °F (478 °C)

SECTION 10. Stability and reactivity

Reactivity

Forms explosive mixtures with air on intense heating.

Chemical stability

Sensitivity to light
Sensitive to air.

Possibility of hazardous reactions

Violent reactions possible with:

Strong oxidizing agents, Strong acids, strong alkalis, strong reducing agents

Conditions to avoid

Strong heating.

A range from approx. 15 Kelvin below the flash point is to be rated as critical.

Incompatible materials

no information available

Hazardous decomposition products

in the event of fire: See section 5.

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Inhalation, Eye contact, Skin contact

Acute oral toxicity

LD50 rat: 3,062 mg/kg (External MSDS)

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC

No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

MATERIAL SAFETY DATA SHEET
according to the Global Harmonized System

Product number 820356
Product name Methyl cyanoacetate for synthesis

Version 1.0

OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

Hazardous properties cannot be excluded.

Other information

The following applies to cyanogen compounds/ nitriles in general: utmost caution! Release of hydrocyanic acid is possible - blockade of cellular respiration. Cardiovascular disorders, dyspnoea, unconsciousness.

Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

Partition coefficient: n-octanol/water

log Pow: -0.47

(experimental)

Bioaccumulation is not expected (log Pow <1).

Mobility in soil

No information available.

Other adverse effects

Additional ecological information

We have no quantitative data concerning the ecological effects of this product.

Further information on ecology

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

MATERIAL SAFETY DATA SHEET
according to the Global Harmonized System

Product number 820356
Product name Methyl cyanoacetate for synthesis

Version 1.0

SECTION 14. Transport information

Land transport (DOT)

Not classified as dangerous in the meaning of transport regulations.

Air transport (IATA)

Not classified as dangerous in the meaning of transport regulations.

Sea transport (IMDG)

Not classified as dangerous in the meaning of transport regulations.

SECTION 15. Regulatory information

United States of America

Canada

WHMIS Classification

Not controlled under WHMIS (Canada).

This product has been classified according to the hazard criteria of the CPR and the MSDS contains all of the information required by the CPR.

Notification status

TSCA: On TSCA Inventory

DSL: This product contains one or several components listed in the Canadian NDSL.
Ingredients
Methyl cyanoacetate

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Date of issue: 02/04/2013

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.
