
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB300-664

## NB300-664

# Baboon Antibody



## Unit Size
0.1 mg

## Concentration
Please see the vial label for concentration.

## Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

## Applications
WB, ICC/IF, IP

## Species
Drosophila

## Host
Rabbit

## Clonality
Polyclonal

## Purity
Affinity purified

## Preservative
No Preservative

Updated 3/9/2013 2.0

## Specificity/Sensitivity
The is unique to Baboon protein.


## Immunogen
Synthetic peptide: CNKNENMKRIFETDYVPHRLTS, corresponding to N terminal amino acids 200-221 of Drosophilia melanogaster Baboon. The peptide was amidated for conjugation.

## Recommended Dilutions
Immunoprecipitation, Western Blot 1:500, Immunocytochemistry/Immunofluorescence

## Buffer
BSA, Glycerol, Ethalene glycol. pH 7.4

## Uses
Immunocytochemistry, Immunoprecipitation, Western Blot Detects a band of approximately 73 kDa. Optimal dilutions and concentrations should be determined by the end user.

## Images
Western Blot: Baboon Antibody [NB300-664] - Lane 1 and 2 : Cells expressing Baboon A. Lane 3: mock trasfected cells



*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months.* ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

**Novus USA**
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

**Novus Canada**
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

**Novus Europe**
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com