



Mouse anti-HA (haemagglutinin) tag (YPYDVPDYA) IgG conjugated to APC

Product Number D3-1722-100
Amount 100 µg
Clone 16B12
Store at 2-8°C

Form/Shipping & Storage

Supplied as a lyophilized powder. Upon receipt, store at 2-8°C in the dark, do not freeze. Phycobiliproteins are sensitive to freeze-thaw cycles.

Handling

Reconstitute to 1.0 ml with distilled deionized water vortex gently and allow vial to sit on ice for 20 minutes. We recommend that the investigator determine the appropriate working concentration for their specific application.

Avoid exposure to heat and light.

Buffer

Upon rehydration with 1.0 ml distilled deionized water; the product is in 100 mM sodium phosphate (pH 7.4), 50 mM sucrose, 150 mM sodium chloride, 0.1% BSA as a stabilizer, and 0.05% sodium azide as a preservative. The concentration of the conjugate is 100 µg/ml

Stability

Lyophilized material is stable for up to one year. After product has been reconstituted, product should be stored at 2-8°C in the dark and be used within 6

months. If further dilution of the conjugate is required, use diluted material within one month.

Note

For research use only, not for diagnostic or therapeutic use.

Spectral Characteristics

Visible absorption maxima	650
Emission maximum	673

Concentration

After reconstitution to 1.0 ml

References:

Nygard NR, Bono C, Brown LR, Gorka J, Giacoletto KS, Schaiff WT, Graham MB, McCourt DW, Kabeer M, Braciale VL, et al. Antibody recognition of an immunogenic influenza hemagglutinin-human leukocyte antigen class II complex. J Exp Med. 1991 Jul 1;174(1):243-51.

Rogers BE, Chaudhuri TR, Reynolds PN, Della Manna D, Zinn KR. Non-invasive gamma camera imaging of gene transfer using an adenoviral vector encoding an epitope-tagged receptor as a reporter. Gene Ther. 2003 Jan;10(2):105-14.



COLUMBIA BIOSCIENCES