



## **Rabbit anti-S tag conjugated to Dylight® 550**

Product Number      D9-1831  
Amount                0.1 mg total protein  
Antigen                Amino acid sequence KETAAAKFERQHMS  
Store at                2-8°C

### Form/Shipping & Storage

Supplied liquid at 1mg/mL. Upon receipt, store at 2-8 °C. Fluorescent dyes are sensitive to light. Please store in the dark and avoid exposure to sunlight.

### Handling

We recommend that the investigator determine the appropriate working concentration for their specific application.

### Buffer

0.1M sodium phosphate, 0.15M NaCl, pH7.4, 1% BSA, 0.02% NaN<sub>3</sub>

### Stability


Product should be stored at 2-8°C in the dark and be used within 1 year. If further dilution of the conjugate is required, use diluted material within one month.

### Note

For research use only, not for diagnostic or therapeutic use.

### Spectral Characteristic

Visible absorption maxima      562 nm  
Emission maximum                576 nm



### References

Plagmann I, Chalaris A, Kruglov AA, Nedospasov S, Rosenstiel P, Rose-John S, Scheller J. Transglutaminase-catalyzed covalent multimerization of Camelidae anti-human TNF single domain antibodies improves neutralizing activity. J Biotechnol. 2009 Jun 15;142(2):170-8.

Carson SD, Kim KS, Pirruccello SJ, Tracy S, Chapman NM. Endogenous low-level expression of the coxsackievirus and adenovirus receptor enables coxsackievirus B3 infection of RD cells. J Gen Virol. 2007 Nov;88(Pt 11):3031-8.

Cao L, Shen G, Zhu Y, Wang W, Zhao X, Ye Q, Zhu H, Lu Z, Si J. Characterization of a single-chain variable fragment (scFv) antibody directed against the human asialoglycoprotein receptor. Biotechnol Appl Biochem. 2006 May;44(Pt 2):65-72.



**COLUMBIA BIOSCIENCES**