



## **Mouse anti-HA (haemagglutinin) tag (YPYDVPDYA) IgG conjugated to HRP**

Product Number    HRP-1722  
Lot #                HRP034-13-001  
Amount             100 µg  
Clone                16B12  
Store at             2-8°C

### Form/Shipping & Storage

Supplied as a lyophilized powder. Upon receipt, store at 2-8°C in the dark, do not freeze. Proteins are sensitive to freeze-thaw cycles.

### Handling

Reconstitute to 1.0 ml with distilled deionized water vortex gently and allow vial to sit on ice for 20 minutes. We recommend that the investigator determine the appropriate working concentration for their specific application. Avoid exposure to heat and light.

### Buffer

Upon rehydration with 1.0 ml distilled deionized water; The product is in 100 mM NaPO<sub>4</sub> (pH 7.4) + 100 mM NaCl + 1.5% BSA, 0.01% Thimerosal + 50mM Sucrose

### Stability

Lyophilized material is stable for up to one year. After product has been reconstituted, product should be stored at 2-8°C in the dark and be used within 6

months. If further dilution of the conjugate is required, use diluted material within one week.

### Note

For research use only, not for diagnostic or therapeutic use.

### Concentration

After reconstitution - 0.1 mg/mL

### References:

Nygard NR, Bono C, Brown LR, Gorka J, Giacometto KS, Schaiff WT, Graham MB, McCourt DW, Kabeer M, Braciale VL, et al. Antibody recognition of an immunogenic influenza hemagglutinin-human leukocyte antigen class II complex. J Exp Med. 1991 Jul 1;174(1):243-51.

Rogers BE, Chaudhuri TR, Reynolds PN, Della Manna D, Zinn KR. Non-invasive gamma camera imaging of gene transfer using an adenoviral vector encoding an epitope-tagged receptor as a reporter. Gene Ther. 2003 Jan;10(2):105-14.



**COLUMBIA BIOSCIENCES**