

SAFETY DATA SHEET

1. Identification

Product identifier: 2-PROPANOL

Other means of identification

Product No.: 9088, 5892, 9095, 9084, 9083, 9082, 9079, 9078, 9059, 9055, 9045, 5986, 5978, 5977, 5967, 5873, 5863, 9827, 5373, 9334

Recommended use and restriction on use

Recommended use: Not available.

Restrictions on use: Not known.

Manufacturer/Importer/Supplier/Distributor information

Manufacturer

Company Name: Avantor Performance Materials, Inc.
Address: 3477 Corporate Parkway, Suite 200
Center Valley, PA 18034

Telephone: Customer Service: 855-282-6867

Fax:
Contact Person: Environmental Health & Safety
e-mail: info@avantormaterials.com

Emergency telephone number:

24 Hour Emergency: 908-859-2151

Chemtrec: 800-424-9300

2. Hazard(s) identification

Hazard classification

Physical hazards

Flammable liquids	Category 2
-------------------	------------

Health hazards

Serious eye damage/eye irritation	Category 2A
Specific target organ toxicity - single exposure	Category 3

Label elements

Hazard symbol:



Signal word: Danger

Hazard statement: Highly flammable liquid and vapor.
Causes serious eye irritation.
May cause respiratory irritation.
May cause drowsiness or dizziness.

Precautionary statement

- Prevention:** Keep away from heat/sparks/open flames/hot surfaces. No smoking. Keep container tightly closed. Ground/bond container and receiving equipment. Use explosion-proof electrical/ventilating/lighting/equipment. Use only non-sparking tools. Take precautionary measures against static discharge. Wear protective gloves/protective clothing/eye protection/face protection. Use only outdoors or in a well-ventilated area. Avoid breathing dust/mist/vapors. Wash thoroughly after handling.
- Response:** In case of fire: Use water spray, foam, dry powder or carbon dioxide for extinction. IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell. IF ON SKIN (or hair): Remove/take off immediately all contaminated clothing. Rinse skin with water/shower. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
- Storage:** Store in a well-ventilated place. Keep cool. Keep container tightly closed. Store locked up.
- Disposal:** Dispose of contents/container to an appropriate treatment and disposal facility in accordance with applicable laws and regulations, and product characteristics at time of disposal.
- Other hazards which do not result in GHS classification:** Static accumulating flammable liquid can become electrostatically charged even in bonded and grounded equipment. Sparks may ignite liquid and vapor. May cause flash fire or explosion.

3. Composition/information on ingredients

Substances

Chemical identity	Common name and synonyms	CAS number	Content in percent (%)*
ISOPROPYL ALCOHOL		67-63-0	98 - 100%

* All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

4. First-aid measures

- General information:** Get medical advice/attention if you feel unwell. Show this safety data sheet to the doctor in attendance.
- Ingestion:** Call a physician or poison control center immediately. Do NOT induce vomiting. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.
- Inhalation:** Move to fresh air. Get medical attention if symptoms persist.
- Skin contact:** Wash skin thoroughly with soap and water. Get medical attention if symptoms occur.
- Eye contact:** Immediately flush with plenty of water for at least 15 minutes. If easy to do, remove contact lenses. Get medical attention.

Most important symptoms/effects, acute and delayed

- Symptoms:** Harmful if swallowed. Narcotic effect. Irritating to eyes, respiratory system and skin.

Indication of immediate medical attention and special treatment needed

Treatment: Treat symptomatically. Symptoms may be delayed.

5. Fire-fighting measures

General fire hazards: Highly flammable liquid and vapour.

Suitable (and unsuitable) extinguishing media

Suitable extinguishing media: Water spray, foam, dry powder or carbon dioxide.

Unsuitable extinguishing media: Avoid water in straight hose stream; will scatter and spread fire.

Specific hazards arising from the chemical: Vapors may cause a flash fire or ignite explosively. Vapors may travel considerable distance to a source of ignition and flash back. Prevent buildup of vapors or gases to explosive concentrations. Vapor from the solvent may accumulate in container headspace resulting in flammability hazard.

Special protective equipment and precautions for firefighters

Special fire fighting procedures: Use water spray to keep fire-exposed containers cool. Water may be ineffective in fighting the fire. Fight fire from a protected location. Move containers from fire area if you can do so without risk.

Special protective equipment for fire-fighters: Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures: ELIMINATE all ignition sources (no smoking, flares, sparks or flames in immediate area). Keep unauthorized personnel away. Keep upwind. Use personal protective equipment. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. See Section 8 of the MSDS for Personal Protective Equipment.

Methods and material for containment and cleaning up: Eliminate all ignition sources if safe to do so. Take precautionary measures against static discharges. Stop leak if possible without any risk. Use only non-sparking tools. Absorb spill with vermiculite or other inert material, then place in a container for chemical waste. Clean surface thoroughly to remove residual contamination. Dike far ahead of larger spill for later recovery and disposal.

Notification Procedures: Prevent entry into waterways, sewer, basements or confined areas. Inform authorities if large amounts are involved.

Environmental precautions: Do not contaminate water sources or sewer. Prevent further leakage or spillage if safe to do so.

7. Handling and storage

Precautions for safe handling: DO NOT handle, store or open near an open flame, sources of heat or sources of ignition. Protect material from direct sunlight. Take precautionary measures against static discharges. Ground/bond container and receiving equipment. Use explosion-proof electrical/ventilating/lighting/equipment. Use only non-sparking tools. Wear protective gloves/protective clothing/eye protection/face protection. Avoid contact with eyes, skin, and clothing. Use only with adequate ventilation. Wash hands thoroughly after handling.

Conditions for safe storage, including any incompatibilities: Keep away from food, drink and animal feeding stuffs. Keep container tightly closed in a cool, well-ventilated place. Ground container and transfer equipment to eliminate static electric sparks. Comply with all national, state, and local codes pertaining to the storage, handling, dispensing, and disposal of flammable liquids.

8. Exposure controls/personal protection

Control parameters

Occupational exposure limits

Chemical identity	Type	Exposure Limit values	Source
ISOPROPYL ALCOHOL	TWA	200 ppm	US. ACGIH Threshold Limit Values (2011)
	STEL	400 ppm	US. ACGIH Threshold Limit Values (2011)
	REL	400 ppm 980 mg/m3	US. NIOSH: Pocket Guide to Chemical Hazards (2010)
	STEL	500 ppm 1,225 mg/m3	US. NIOSH: Pocket Guide to Chemical Hazards (2010)
	PEL	400 ppm 980 mg/m3	US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000) (02 2006)
	TWA	400 ppm 980 mg/m3	US. OSHA Table Z-1-A (29 CFR 1910.1000) (1989)
	STEL	500 ppm 1,225 mg/m3	US. OSHA Table Z-1-A (29 CFR 1910.1000) (1989)

Biological limit values

Chemical identity	Exposure Limit values	Source
ISOPROPYL ALCOHOL (acetone: Sampling time: End of shift at end of work week.)	40 mg/l (Urine)	ACGIH BEL (2011)

Appropriate engineering controls No data available.

Individual protection measures, such as personal protective equipment

General information: Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. An eye wash and safety shower must be available in the immediate work area. Use explosion-proof ventilation equipment.

Eye/face protection: Wear safety glasses with side shields (or goggles).

Skin protection

Hand protection: Chemical resistant gloves

Other: Wear suitable protective clothing.

Respiratory protection: In case of inadequate ventilation use suitable respirator.

Hygiene measures: Provide eyewash station and safety shower. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing to remove contaminants. Discard contaminated footwear that cannot be cleaned.

9. Physical and chemical properties

Appearance

Physical state:	Liquid
Form:	Liquid
Color:	Colorless
Odor:	Odor of rubbing alcohol
Odor threshold:	No data available.
pH:	No data available.
Melting point/freezing point:	-88.5 °C
Initial boiling point and boiling range:	82 °C (101.3 kPa)
Flash Point:	12 °C (Closed Cup)
Evaporation rate:	2.8 n-butyl acetate=1
Flammability (solid, gas):	Class IB Flammable Liquid
Upper/lower limit on flammability or explosive limits	
Flammability limit - upper (%):	12.7 %(V)
Flammability limit - lower (%):	2 %(V)
Explosive limit - upper (%):	No data available.
Explosive limit - lower (%):	No data available.
Vapor pressure:	6.0 kPa (25 °C)
Vapor density:	2.1 AIR=1
Relative density:	0.79 (20 °C)
Solubility(ies)	
Solubility in water:	Miscible with water.
Solubility (other):	No data available.
Partition coefficient (n-octanol/water):	0.05
Auto-ignition temperature:	399 °C
Decomposition temperature:	No data available.
Viscosity:	No data available.
Other information	
Molecular weight:	60.1 g/mol (C ₃ H ₈ O)

10. Stability and reactivity

Reactivity:	No dangerous reaction known under conditions of normal use.
Chemical stability:	Material is stable under normal conditions.
Possibility of hazardous reactions:	Hazardous polymerization does not occur.
Conditions to avoid:	Heat, sparks, flames. Sunlight.
Incompatible materials:	Strong oxidizing agents. Acetylene. Acids. Chlorine. Hydrogen peroxide (H ₂ O ₂) Ethylene Oxide Sulfuric acid. Isocyanates. Aluminum.
Hazardous decomposition products:	Thermal decomposition may release oxides of carbon.

11. Toxicological information

Information on likely routes of exposure

Ingestion:	Irritating. May cause nausea, stomach pain and vomiting.
Inhalation:	May cause irritation to the mucous membranes and upper respiratory tract.
Skin contact:	Prolonged or repeated skin contact may cause drying, cracking, or irritation.
Eye contact:	Causes serious eye irritation.

Information on toxicological effects

Acute toxicity (list all possible routes of exposure)

Oral	
Product:	LD 50 (Rat): 5,045 mg/kg
Dermal	
Product:	LD 50 (Rabbit): 12,800 mg/kg

Inhalation	
Product:	No data available.

Repeated dose toxicity	
Product:	No data available.

Skin corrosion/irritation	
Product:	Prolonged or repeated skin contact may cause drying, cracking, or irritation.

Serious eye damage/eye irritation	
Product:	Causes serious eye irritation.

Respiratory or skin sensitization	
Product:	Not a skin sensitizer.

Carcinogenicity	
Product:	This substance has no evidence of carcinogenic properties.

IARC Monographs on the Evaluation of Carcinogenic Risks to Humans:
No carcinogenic components identified

US. National Toxicology Program (NTP) Report on Carcinogens:
No carcinogenic components identified

US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050):
No carcinogenic components identified

Germ cell mutagenicity

In vitro	
Product:	No data available.

In vivo	
Product:	No data available.

Reproductive toxicity	
Product:	No components toxic to reproduction

Specific target organ toxicity - single exposure	
Product:	Narcotic effect. Respiratory tract irritation.

Specific target organ toxicity - repeated exposure

Product:	None known.
Aspiration hazard	
Product:	May be harmful if swallowed and enters airways.
Other effects:	None known.

12. Ecological information

Ecotoxicity:

Acute hazards to the aquatic environment:

Fish

Product: LC 50 (Western mosquitofish (*Gambusia affinis*), 96 h): > 1,400 mg/l

Aquatic invertebrates

Product: LC 50 (Water flea (*Daphnia magna*), 24 h): 10,000 mg/l

Chronic hazards to the aquatic environment:

Fish

Product: No data available.

Aquatic invertebrates

Product: No data available.

Toxicity to Aquatic Plants

Product: No data available.

Persistence and degradability

Biodegradation

Product: Expected to be readily biodegradable.

BOD/COD ratio

Product: No data available.

Bioaccumulative potential

Bioconcentration factor (BCF)

Product: No data available on bioaccumulation.

Partition coefficient n-octanol / water (log Kow)

Product: Log Kow: 0.05

Mobility in soil:

The product is partly soluble in water. May spread in the aquatic environment.

Other adverse effects:

The product components are not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

13. Disposal considerations

Disposal instructions:

Discharge, treatment, or disposal may be subject to national, state, or local laws.

Contaminated packaging:

Since emptied containers retain product residue, follow label warnings even after container is emptied.

14. Transport information

DOT

UN number:	UN 1219
UN proper shipping name:	Isopropanol
Transport hazard class(es)	
Class(es):	3
Label(s):	3
Packing group:	II
Marine Pollutant:	No

IMDG

UN number:	UN 1219
UN proper shipping name:	ISOPROPANOL
Transport hazard class(es)	
Class(es):	3
Label(s):	3
EmS No.:	F-E, S-D
Packing group:	II
Marine Pollutant:	No

IATA

UN number:	UN 1219
Proper Shipping Name:	Isopropanol
Transport hazard class(es):	
Class(es):	3
Label(s):	3
Marine Pollutant:	No
Packing group:	II

15. Regulatory information

US federal regulations

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

None present or none present in regulated quantities.

CERCLA Hazardous Substance List (40 CFR 302.4):

ISOPROPYL ALCOHOL Reportable quantity: 100 lbs.

Superfund amendments and reauthorization act of 1986 (SARA)

Hazard categories

Acute (Immediate) Chronic (Delayed) Fire Reactive Pressure Generating

SARA 302 Extremely hazardous substance

None present or none present in regulated quantities.

SARA 304 Emergency release notification

Chemical identity	RQ
ISOPROPYL ALCOHOL	100 lbs.

SARA 311/312 Hazardous chemical

Chemical identity	Threshold Planning Quantity
ISOPROPYL ALCOHOL	500 lbs

SARA 313 (TRI reporting)

Chemical identity	Reporting threshold for other users	Reporting threshold for manufacturing and processing
ISOPROPYL ALCOHOL	10000 lbs	25000 lbs.

Clean Water Act Section 311 Hazardous Substances (40 CFR 117.3)

None present or none present in regulated quantities.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130):

None present or none present in regulated quantities.

US state regulations

US. California Proposition 65

No ingredient regulated by CA Prop 65 present.

US. New Jersey Worker and Community Right-to-Know Act

ISOPROPYL ALCOHOL Listed

US. Massachusetts RTK - Substance List

ISOPROPYL ALCOHOL Listed

US. Pennsylvania RTK - Hazardous Substances

ISOPROPYL ALCOHOL Listed

US. Rhode Island RTK



ISOPROPYL ALCOHOL Listed

Inventory Status:

Australia AICS:	On or in compliance with the inventory
Canada DSL Inventory List:	On or in compliance with the inventory
EU EINECS List:	On or in compliance with the inventory
EU ELINCS List:	Not in compliance with the inventory.
Japan (ENCS) List:	On or in compliance with the inventory
EU No Longer Polymers List:	Not in compliance with the inventory.
China Inv. Existing Chemical Substances:	On or in compliance with the inventory
Korea Existing Chemicals Inv. (KECI):	On or in compliance with the inventory
Canada NDSL Inventory:	Not in compliance with the inventory.
Philippines PICCS:	On or in compliance with the inventory
US TSCA Inventory:	On or in compliance with the inventory
New Zealand Inventory of Chemicals:	On or in compliance with the inventory
Switzerland Consolidated Inventory:	Not in compliance with the inventory.
Japan ISHL Listing:	On or in compliance with the inventory
Japan Pharmacopoeia Listing:	Not in compliance with the inventory.

16. Other information, including date of preparation or last revision

NFPA Hazard ID



Special hazard.

Hazard rating: 0 - Minimal; 1 - Slight; 2 - Moderate; 3 - Serious; 4 - Severe

Issue date: 06-23-2014**Revision date:** No data available.**Version #:** 1.1**Further information:** No data available.

Disclaimer: THE INFORMATION PRESENTED IN THIS MATERIAL SAFETY DATA SHEET (MSDS/SDS) WAS PREPARED BY TECHNICAL PERSONNEL BASED ON DATA THAT THEY BELIEVE IN THEIR GOOD FAITH JUDGMENT IS ACCURATE. HOWEVER, THE INFORMATION PROVIDED HEREIN IS PROVIDED "AS IS," AND AVANTOR PERFORMANCE MATERIALS MAKES AND GIVES NO REPRESENTATIONS OR WARRANTIES WHATSOEVER, AND EXPRESSLY DISCLAIMS ALL WARRANTIES REGARDING SUCH INFORMATION AND THE PRODUCT TO WHICH IT RELATES, WHETHER EXPRESS, IMPLIED, OR STATUTORY, INCLUDING WITHOUT LIMITATION<(,<)> WARRANTIES OF ACCURACY, COMPLETENESS, MERCHANTABILITY, NON-INFRINGEMENT, PERFORMANCE, SAFETY, SUITABILITY, STABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, AND ANY WARRANTIES ARISING FROM COURSE OF DEALING, COURSE OF PERFORMANCE, OR USAGE OF TRADE. THIS MSDS/SDS IS INTENDED ONLY AS A GUIDE TO THE APPROPRIATE PRECAUTIONARY HANDLING OF THE MATERIAL BY A PROPERLY TRAINED PERSON USING THIS PRODUCT, AND IS NOT INTENDED TO BE COMPREHENSIVE AS TO THE MANNER AND CONDITIONS OF USE, HANDLING, STORAGE, OR DISPOSAL OF THE PRODUCT. INDIVIDUALS RECEIVING THIS MSDS/SDS MUST ALWAYS EXERCISE THEIR OWN INDEPENDENT JUDGMENT IN DETERMINING THE APPROPRIATENESS OF SUCH ISSUES. ACCORDINGLY, AVANTOR PERFORMANCE MATERIALS ASSUMES NO LIABILITY WHATSOEVER FOR THE USE OF OR RELIANCE UPON THIS INFORMATION. NO SUGGESTIONS FOR USE ARE INTENDED AS, AND NOTHING HEREIN SHALL BE CONSTRUED AS, A RECOMMENDATION TO INFRINGE ANY EXISTING PATENTS OR TO VIOLATE ANY FEDERAL, STATE, LOCAL, OR FOREIGN LAWS. AVANTOR PERFORMANCE MATERIALS REMINDS YOU THAT IT IS YOUR LEGAL DUTY TO MAKE ALL INFORMATION IN THIS MSDS/SDS AVAILABLE TO YOUR EMPLOYEES.