

**NB100-74542****SREBP1 Antibody****Unit Size**

0.1 mg

**Concentration**

Concentrations vary lot to lot. See vial label for concentration.

**Storage**

Store at -20°C. Avoid freeze-thaw cycles.

**Applications**

WB

**Species**

Mouse, Rat

**Host**

Rabbit

**Clonality**

Polyclonal

**Purity**

Immunogen affinity purified

**Preservative**

0.05% Sodium Azide

**Immunogen**

Synthetic peptide corresponding to residues M(a.a. 32) L Q L I N N Q D S D F P G L F(a.a. 47) of mouse SREBP 1.

**Recommended Dilutions**

Western Blot 1:500

**Buffer**

PBS containing 1 mg/ml BSA

**Uses**

This antibody detects an ~68 and 120 kDa protein representing SREBP 1 in mouse and rat liver samples as well as rat kidney samples. A predominant band at ~68 kDa (active cleaved site) is seen and a band at ~120 kDa (inactive precursor) may not be seen or it may be diminished.

**Images**This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: [www.novusbio.com/NB100-74542](http://www.novusbio.com/NB100-74542)

Updated 3/9/2013 2.0

**Limitations:** This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).**

**Novus USA**

8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)

**Novus Canada**

461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)

**Novus Europe**

12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)

