

NB100-65853**ART2.2/Art2b Antibody (Nika102)****Unit Size**

0.125 mg

Concentration

1.0 mg/ml

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

FLOW, IP

Species

Mouse

Host

Rat

Clonality

Monoclonal

Isotype

IgG2a

Purity

Protein G purified

Preservative

0.09% Sodium Azide

Specificity/Sensitivity

NB100-65853 recognizes the gene product of the mouse ADP-ribosyltransferase (ART) 2.2 gene, an ortholog of rat RT6. ART2.2 expressed exclusively by mature T-cells. Levels of ART2.2 expression vary between inbred strains of mice and is absent in NZW mice, in which the ART2.2 gene is deleted (1).

Immunogen


pME.CD8LF-ART2.2

Recommended DilutionsFlow Cytometry
Immunoprecipitation**Buffer**

Phosphate buffered saline pH 7.4

Images

Flow Cytometry: ART2.2/Art2b Antibody (Nika102) [NB100-65853] - Staining of C57Bl/6J mouse spleen cells with RAT ANTI MOUSE ART2.2 antibody (NB100-65853).



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

