
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-58833

NB100-58833

eIF4E Antibody



Unit Size
0.1 ml

Concentration
0.2 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB, IP

Species
Human, Mouse

Molecular Weight
25kDa

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
The immunogen recognized by this antibody maps to a region between residue 167 and 217 of human eukaryotic translation initiation factor using the numbering given in entry NP_001959.1 (GeneID 1977).

Recommended Dilutions
Immunoprecipitation 2-5 ug/mg lysate, Western Blot 1:2000-1:10000

Buffer
Tris-buffered Saline and 0.1% BSA

Uses
Western Blot and Immunoprecipitation

Images
Western Blot: eIF4E Antibody [NB100-58833] - Detection of Human and Mouse eIF4E on HeLa whole cell lysate using NB100-58833. eIF4E was also immunoprecipitated by rabbit anti-eIF4E antibody NB100-58832.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com