

NB100-59833**Cip4 Antibody****Unit Size**

0.1 mg

Concentration

1.0 mg/ml

Storage

Store at 4°C. Do not freeze.

Applications

WB, IP

Species

Human

Host

Rabbit

Clonality

Polyclonal

Purity

Immunogen affinity purified

Preservative

0.09% Sodium Azide

Immunogen

The immunogen recognized by this antibody maps to a region between residue 25 and 75 of human thyroid receptor interacting protein 10 (Cdc42-interacting protein 4) using the numbering given in entry AAM46851.1 (GeneID 9322).

Recommended Dilutions

Immunoprecipitation, Western Blot

Buffer


Tris-citrate/phosphate buffer, pH 7 to 8

Uses

Immunoprecipitation

Images

Western Blot: Cip4 Antibody [NB100-59833] - Detection of Human TRIP10 on HeLa whole cell lysate using NB100-59833. TRIP10 was also immunoprecipitated by rabbit anti-TRIP10 antibody NB100-59834.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

