
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-1617

NB100-1617

TRPV1 Antibody



Unit Size
0.05 ml

Concentration
This product is unpurified. The exact concentration of antibody is not quantifiable.

Storage
Aliquot and store at -20C or -80C. Avoid freeze-thaw cycles.

Applications
WB, ICC/IF, IHC, IHC-Fr, IP

Species
Mouse, Rat

Host
Rabbit

Clonality
Polyclonal

Purity
Whole antisera

Preservative
0.05% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
Vanilloid Receptor 1

Immunogen
Synthetic peptide: RASLDSEESESPPQENSC, corresponding to amino-terminus of Rat VR1, amino acids 4-21.

Recommended Dilutions
Immunohistochemistry-Frozen, Western Blot, Immunoprecipitation, Immunocytochemistry/Immunofluorescence 1/1000, Immunohistochemistry

Buffer
Whole Serum

Uses
Immunohistochemistry and Immunocytochemistry 1:1000. Dilution listed only as a recommendation. Optimal dilution should be determined by investigator.

References (more available at www.novusbio.com/NB100-1617)
Stein, A et al. Phosphoinositide 3-Kinase Binds to TRPV1 Mediates NGF-stimulated TRPV1 Trafficking to the Plasma Membrane. Published online doi:10.1085/jgp.200609576. 2006 Oct 30. [PMID: 17074976

Images
Immunohistochemistry: TRPV1 Antibody [NB100-1617] - Dorsal Root Ganglion



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com