TCI Chemicals (India) Pvt. Ltd.

SAFETY DATA SHEET

According to 1907/2006/EC, Article 31

Revision number: 3 **Revision date:** 10/30/2014

1. IDENTIFICATION

Identification of the substance or preparation

Product name: Hexyl Methacrylate (stabilized with MEHQ)
Product code: M0503

Use of the substance/preparation

Recommended use: Reagents

Company/undertaking identification
TCI Chemicals (India) Pvt. Ltd.
Plot No. B-28, Phase II,
5th Cross Street, MEPZ-SEZ, Tambaram,
Chennai, Tamilnadu - 600045
India
Telephone: +91-44-2262 0909

Emergency telephone number:
+91-44-2262 0909

2. HAZARDS IDENTIFICATION

Indication of danger: Xi - Irritant
R-phrase(s) R36/37/38 - Irritating to eyes, respiratory system and skin.
GHS classification
PHYSICAL HAZARDS
Flammable liquids Category 4
HEALTH HAZARDS
Skin corrosion/irritation Category 2
Serious eye damage/eye irritation Category 2
Skin sensitization Category 1
ENVIRONMENTAL HAZARDS Not classified
GHS label elements, including precautionary statements
Pictograms or hazard symbols



Signal word Warning
Hazard statements
H227-Combustible liquid.
H315-Causes skin irritation.
H319-Causes serious eye irritation.
H317-May cause an allergic skin reaction.

Precautionary statements
[Prevention]
P210-Keep away from flames and hot surfaces.
P261-Avoid breathing dust/fume/gas/mist/vapours/spray.
P272-Contaminated work clothing should not be allowed out of the workplace.
P264-Wash hands thoroughly after handling.
P280-Wear protective gloves/protective clothing/eye protection/face protection.
[Response]
P305+P351+P338-IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337+P313-If eye irritation persists: Get medical advice/attention.
P302+P352-IF ON SKIN: Wash with plenty of soap and water.
P333+P313-If skin irritation or rash occurs: Get medical advice/attention.
P363-Wash contaminated clothing before reuse.
[Storage]
P403+P235-Store in a well-ventilated place. Keep cool.
[Disposal]
P501-Dispose of contents/container through a waste management company authorized by the local government

Other hazards which do not result in classification May cause polimerization.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance/mixture:	Substance
Components:	Hexyl Methacrylate (stabilized with MEHQ)
Percent:	>98.0%(GC)
CAS Number:	142-09-6
EC-No:	205-521-9
Synonyms:	Methacrylic Acid Hexyl Ester (stabilized with MEHQ)
Chemical Formula:	$C_{10}H_{18}O_2$

4. FIRST AID MEASURES

Inhalation:	Remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical advice/attention if you feel unwell.
Skin contact:	Remove/Take off immediately all contaminated clothing. Gently wash with plenty of soap and water. If skin irritation or rash occurs: Get medical advice/attention.
Eye contact:	Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
Ingestion:	Get medical advice/attention if you feel unwell. Rinse mouth.
Protection of first-aiders:	A rescuer should wear personal protective equipment, such as rubber gloves and air-tight goggles.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media:	Dry chemical, foam, carbon dioxide.
Unsuitable extinguishing media:	Water (It may scatter and spread fire.)
Specific hazards arising from the chemical:	This substance may polimerize explosively when heated or involved in a fire. Container may explode when heated. Combat fire from a sheltered position.
Precautions for firefighters:	Fire-extinguishing work is done from the windward and the suitable fire-extinguishing method according to the surrounding situation is used. Uninvolved persons should evacuate to a safe place. In case of fire in the surroundings: Keep containers cool by spraying with water. Eliminate all ignition sources if safe to do so.
Special protective equipment for firefighters:	When extinguishing fire, be sure to wear personal protective equipment.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures:	Use personal protective equipment. Keep people away from and upwind of spill/leak. Ensure adequate ventilation. Entry to non-involved personnel should be controlled around the leakage area by roping off, etc.
Environmental precautions:	Prevent product from entering drains.
Methods and materials for containment and cleaning up:	Absorb spilled material in dry sand or inert absorbent before recovering it into a covered container. In case of large amount of spillage, contain a spill by bunding. Adhered or collected material should be promptly disposed of, in accordance with appropriate laws and regulations.
Prevention of secondary hazards:	Remove all sources of ignition. Fire-extinguishing devices should be prepared in case of a fire. Use spark-proof tools and explosion-proof equipment.

7. HANDLING AND STORAGE

Precautions for safe handling

Technical measures:	Handling is performed in a well ventilated place. Wear suitable protective equipment. Prevent generation of vapour or mist. Keep away from flames and hot surfaces. Take measures to prevent the build up of electrostatic charge. Use explosion-proof equipment. Wash hands and face thoroughly after handling. Use a closed system, ventilation.
Advice on safe handling:	Avoid contact with skin, eyes and clothing.

Conditions for safe storage, including any incompatibilities

Storage conditions:	Keep container tightly closed. Store in a cool, dark and well-ventilated place. Store away from incompatible materials such as oxidizing agents. Light-sensitive
Packaging material:	Comply with laws.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Engineering controls:	Install a closed system or local exhaust as possible so that workers should not be exposed directly. Also install safety shower and eye bath.

Personal protective equipment

Respiratory protection:	Vapor respirator. Follow local and national regulations.
Hand protection:	Protective gloves.
Eye protection:	Safety glasses. A face-shield, if the situation requires.
Skin and body protection:	Protective clothing. Protective boots, if the situation requires.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state (20°C):	Liquid
Form:	Clear
Colour:	Colorless - Almost colorless
Odour:	No data available
pH:	No data available
Melting point/freezing point:	No data available
Boiling point/range:	88°C/2.3kPa

9. PHYSICAL AND CHEMICAL PROPERTIES

Flash point: 80°C
Flammability or explosive limits:

Lower: No data available
Upper: No data available
Vapour pressure: 34.7Pa/20°C
Vapour density: 5.9
Relative density: 0.89
Solubility(ies):

[Water] No data available
[Other solvents]
Soluble: Ether, Benzene, Acetone, Ethanol

10. STABILITY AND REACTIVITY

Chemical stability: Polymerization may occur under the influences of heat, light or on contact with polymelization initiators such as peroxides etc.
Possibility of hazardous reactions: No special reactivity has been reported.
Conditions to avoid: Heat, Open flame, Light
Incompatible materials: Oxidizing agents
Hazardous decomposition products: Carbon monoxide, Carbon dioxide

11. TOXICOLOGICAL INFORMATION

Acute Toxicity:
Skin corrosion/irritation:
Serious eye damage/irritation:
Germ cell mutagenicity:
Carcinogenicity:

Reproductive toxicity:

***We judged that this product was not classified into Class6.1 Toxic Substance of current edition of IATA Dangerous Goods Regulations(DGR) according to acute toxicity values and/or Quantitative Structure-Activity Relationship(QSAR).**

12. ECOLOGICAL INFORMATION

Ecotoxicity:
Fish: No data available
Crustacea: No data available
Algae: No data available
Persistence / degradability: No data available
Bioaccumulative potential(BCF): No data available
Mobility in soil

Log Pow: No data available
Soil adsorption (Koc): No data available
Henry's Law constant(PaM^3/mol): No data available
Water Hazard Classes (WGK) : Class 2 - Hazard to waters

13. DISPOSAL CONSIDERATIONS

Recycle to process, if possible. Consult your local regional authorities. You may be able to burn in a chemical incinerator equipped with an afterburner and scrubber system. Observe all federal, state and local regulations when disposing of the substance.

14. TRANSPORT INFORMATION

UN-No: Not listed

ADR/RID
Hazards Class: Does not correspond to the classification standard of the United Nations

IMDG/IMO
Hazards Class: Does not correspond to the classification standard of the United Nations

ICAO/IATA
Hazards Class: Does not correspond to the classification standard of the United Nations

This substance is not regulated by IATA/ICAO/ARD/RID/IMO/IMDG and is considered to be Non Hazardous for transport by Air/Rail/Road/Sea

15. REGULATORY INFORMATION

Indication of danger:
Xi - Irritant
In accordance with local and national regulations
R-phrase(s) R36/37/38 - Irritating to eyes, respiratory system and skin.
S-phrase(s) S26 - In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S28 - After contact with skin, wash immediately with plenty of soap and water.
S36 - Wear suitable protective clothing.

16. OTHER INFORMATION

Prepared by: TCI Chemicals (India) Pvt. Ltd.
Issue date: 10/30/2014

This SDS was prepared sincerely on the basis of the information we could obtained, however, any warranty shall not be given regarding the data contained and the assessment of hazards and toxicity. To the best of our knowledge, the chemical, physical, and toxicological properties have not been thoroughly investigated. Prior to use, please investigate not only the hazards and toxicity information but also the laws and regulations of the organization, area and country where the products are to be used, which shall be given the first priority.
The products are supposed to be used promptly after purchase in consideration of safety. Some new information or amendments may be added afterwards. If the products are to be used far behind the expected time of use or you have any questions, please feel free to contact us. The stated cautions are for normal handling only. In case of special handling, sufficient care should be taken, in addition to the safety measures suitable for the situation. All chemical products should be treated with the recognition of "having unknown hazards and toxicity", which differ greatly depending on the conditions and handling when in use and/or the conditions and duration of storage. The products must be handled only by those who are familiar with specialized knowledge and have experience or under the guidance of those specialists throughout use from opening to storage and disposal. Safe usage conditions shall be set up on each user's own responsibility.