
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-485C

NB100-485C

Von Hippel Lindau Antibody [DyLight 650]



Unit Size
0.1 ml

Concentration
1.0 mg/ml

Storage
Store at 4C in the dark.

Applications
WB

Species
Human

Host
Rabbit

Clonality
Polyclonal

Conjugate
DyLight 650

Purity
Protein A purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Immunogen
A synthetic peptide common to both human and mouse VHL protein.

Recommended Dilutions
Western Blot 1:500-1:1000

Buffer
50mM sodium borate

Uses
This antibody is useful for Western blot where a band ~21kDa is seen. The theoretical molecular weight of VHL is 24 kDa. However, different migrating species ranging from 21-30 kDa have been observed using antibodies to VHL, and may result from a variety of factors including alternatively spliced VHL mRNAs and protein degradation. Other applications have not been tested. Suggested working dilutio... See more at www.novusbio.com/NB100-485C

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-485C

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com