
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-600G

## NB100-600G

# BRCA1 Antibody (MU) [DyLight 488]



### Unit Size
0.1 ml

### Concentration
1.9 mg/ml

### Storage
Store at 4C in the dark.

### Applications
WB, ICC/IF, IP

### Species
Human

### Host
Mouse

### Clonality
Monoclonal

### Isotype
IgG2b Kappa

### Conjugate
DyLight 488

### Purity
Protein G purified

### Preservative
No Preservative

Updated 3/9/2013 2.0

### Specificity/Sensitivity
This recognizes the epitope aa1600-1749.

### Immunogen
Human BRCA1 (residues 1314-1864).

### Recommended Dilutions
immunofluorescence , immunoprecipitation , Western Blot 2-4 ug/ml

### Buffer
50mM sodium borate

### Uses
A band can be seen ~220-240 kDa in Western blot. The investigator should determine the optimal working dilution for a specific application.

### Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-600G

*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months.* ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

**Novus USA**
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

**Novus Canada**
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

**Novus Europe**
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com