RICCA CHEMICAL COMPANY®

Safety Data Sheet

SECTION 1: Identification

1.1. Product Identifier

Trade Name or Designation: Sodium Hydroxide, 0.500 Normal (N/2) in Methanol

Product Number: 7473

Other Identifying Product Numbers: 7473-1, 7473-32

1.2. Recommended Use and Restrictions on Use

General Laboratory Reagent

1.3. Details of the Supplier of the Safety Data Sheet

Company: Ricca Chemical Company

Address: 448 West Fork Drive
Arlington, TX 76012 USA

Telephone: 888-467-4222

1.4. Emergency Telephone Number (24 hr)

CHEMTREC (USA) 800-424-9300

CHEMTREC (International) 1+ 703-527-3887

Safety Data Sheet

SECTION 2: Hazard(s) Identification

2.1. Classification of the Substance or Mixture (in accordance with OSHA HCS 29 CFR 1910.1200)

For the full text of the Hazard and Precautionary Statements listed below, see Section 16.

Hazard Class	Category	Hazard Statement	Precautionary Statements
Acute Toxicity - Oral	Category 3	H301	P264, P270, P301+P310, P321, P330, P405, P501
Acute Toxicity - Dermal	Category 3	H311	P280, P302+P352, P312, P321, P361, P405, P501
Acute Toxicity - Inhalation	Category 3	H331	P261, P271, P304+P340, P311, P321, P403+P233, P405, P501
Skin Corrosion / Irritation	Category 1	H314	P260, P264, P280, P301+P330+P331, P303+P361+P353, P363, P304+P340, P310, P321, P305+P351+P338, P405, P501
Eye Damage / Irritation	Category 1	H318	P280, P305+P351+P338, P310
Reproductive Toxicity	Category 1	H360	P201, P202, P280, P308+P313, P405, P501
Specific Target Organs/Systemic Toxicity Following Single Exposure	Category 1	H370	P260, P264, P270, P307+P311, P321, P405, P501
Specific Target Organs/Systemic Toxicity Following Repeated Exposure	Category 1	H372	P260, P264, P270, P314, P501
Flammable Liquids	Category 2	H225	P210, P233, P240, P241, P242, P243, P280, P303+P361+P353, P370+P378, P403+P235, P501
Corrosive to Metals	Category 1	H290	P234, P390, P406

2.2. GHS Label Elements

Pictograms:



Signal Word: **Danger**

Safety Data Sheet

Hazard Statements:

Hazard Number	Hazard Statement
H225	Highly flammable liquid and vapor.
H290	May be corrosive to metals.
H301	Toxic if swallowed.
H311	Toxic in contact with skin.
H314	Causes severe skin burns and eye damage.
H318	Causes serious eye damage.
H331	Toxic if inhaled.
H360	May damage fertility or the unborn child.
H370	Causes damage to organs.
H372	Causes damage to organs through prolonged or repeated exposure.

Safety Data Sheet

Precautionary Statements:

Precautionary Number	Precautionary Statement
P201	Obtain special instructions before use.
P202	Do not handle until all safety precautions have been read and understood.
P210	Keep away from heat, sparks and open flame. No smoking.
P233	Keep container tightly closed.
P234	Keep only in original container.
P240	Ground container and receiving equipment.
P241	Use explosion-proof equipment.
P242	Use only non-sparking tools.
P243	Take precautionary measures against static discharge.
P260	Do not breathe dust, fumes or mist.
P261	Avoid breathing dust, fumes or mist.
P264	Wash arms, hands and face thoroughly after handling.
P270	Do not eat, drink or smoke when using this product.
P271	Use only outdoors or in a well-ventilated area.
P280	Wear protective gloves and eye protection.
P301+P310	IF SWALLOWED: Immediately call a POISON CENTER or physician.
P301+P330+P331	IF SWALLOWED: rinse mouth. Do NOT induce vomiting.
P302+P352	IF ON SKIN: Wash with plenty of soap and water.
P303+P361+P353	IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water.
P304+P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P307+P311	IF exposed: Call a POISON CENTER or physician.
P308+P313	IF exposed or concerned: Get medical attention.
P310	Immediately call a POISON CENTER or physician.
P311	Call a POISON CENTER or physician.
P312	Call a POISON CENTER or physician if you feel unwell.
P314	Get medical attention if you feel unwell.
P321	Specific treatment (Wash areas of contact with water immediately).
P330	Rinse mouth.
P361	Take off immediately all contaminated clothing and wash it before reuse.
P363	Wash contaminated clothing before reuse.
P390	Absorb spillage to prevent material damage.
P403+P233	Store in a well-ventilated place. Keep container tightly closed.
P405	Store locked up.
P406	Store in corrosive resistant container with a resistant inner liner.
P501	Dispose of contents in accordance with local, state, federal and international regulations.

2.3. WHMIS Classification

WHMIS classification is not included based on the recommended option (Option 4) found in the Canada Gazette Part II, Vol. 149, No.3, page 458

2.4. Hazards not Otherwise Classified or Covered by GHS

Data not available.

SECTION 3: Composition / Information on Ingredients

3.1. Components of Substance or Mixture

Chemical Name	Formula	Molecular Weight	CAS Number	Weight%
Methyl Alcohol	CH_3OH	32.04 g/mol	67-56-1	97.45%
Sodium Hydroxide	NaOH	39.99 g/mol	1310-73-2	2.55%

SECTION 4: First-Aid Measures

4.1. General First Aid Information

Eye Contact: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. May cause irritation with burning and stinging with possible damage to the cornea and conjunctiva.

Inhalation: IF INHALED: Remove person to fresh air and keep comfortable for breathing.

Skin Contact: IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water. Results in drying and cracking which can lead to secondary infections and dermatitis. Dermal absorption causes many of the symptoms of inhalation.

Ingestion: IF SWALLOWED: rinse mouth. Do NOT induce vomiting. Dilute immediately with water or milk. Induce vomiting. Call a physician.

4.2. Most Important Symptoms and Effects, Acute and Delayed

DANGER! Flammable and corrosive. Keep away from heat, sparks and open flames. Keep container closed. Use with adequate ventilation. Avoid ingestion, prolonged breathing of vapor, or contact with skin, eyes or clothing. If ingested, give large quantity of water and call a physician immediately. Wash areas of contact with plenty of water for 15 minutes. For eyes, get medical attention. EYE CONTACT: May cause irritation with burning and stinging with possible damage to the cornea and conjunctiva. SKIN CONTACT: Results in drying and cracking which can lead to secondary infections and dermatitis. Dermal absorption causes many of the symptoms of inhalation.

4.3. Medical Attention or Special Treatment Needed

Immediately call a POISON CENTER or physician. Specific treatment (Wash areas of contact with water immediately).

SECTION 5: Fire-Fighting Measures

5.1. Extinguishing Media

Use any means suitable for extinguishing surrounding fire.

5.2. Specific Hazards Arising from the Substance or Mixture

Highly flammable liquid and vapor. Moderate explosion hazard and dangerous fire hazard when exposed to heat, sparks and open flames. Above flash point, vapor-air mixtures are explosive within flammable limits noted above. Sensitive to static discharge.

5.3. Special Protective Equipment for Firefighters

Wear full protective clothing and NIOSH-approved self-contained breathing apparatus with full facepiece operated in the pressure demand or other positive pressure mode.

SECTION 6: Accidental Release Measures

6.1. Personal Precautions, Protective Equipment and Emergency Procedures

Ground container and receiving equipment. Use explosion-proof equipment. Use only non-sparking tools. Take precautionary measures against static discharge. Wear protective gloves and eye protection.

6.2. Cleanup and Containment Methods and Materials

Remove all sources of ignition. Contain spill. Do not flush to sewer. Absorb with suitable inert material (vermiculite, dry sand, etc) and place in a chemical waste container for proper disposal in an approved waste disposal facility. Ventilate area of spill. Have extinguishing agent available in case of fire. Use non-sparking tools and equipment. Dispose of in accordance with local regulations.

SECTION 7: Handling and Storage

7.1. Precautions for Safe Handling and Storage Conditions

Store in corrosive resistant container with a resistant inner liner. As with all chemicals, wash hands thoroughly after handling. Avoid contact with eyes and skin. Protect from freezing and physical damage. Store in secure, flammable storage area away from all sources of ignition. Empty containers may be hazardous since they retain product residues.

SECTION 8: Exposure Controls / Personal Protection

8.1. Control Parameters

Chemical Name	Limit Type	Country	Exposure Limit	Information Source
Methyl Alcohol (67-56-1)	TWA	USA	200 ppm TWA 260 mg/m³ TWA	U.S. - OSHA - Final PELs - Time Weighted Averages (TWAs)
Methyl Alcohol (67-56-1)	TLV-STEL	USA	250 ppm STEL	ACGIH - Threshold Limit Values - Short Term Exposure Limits (TLV-STEL)
Methyl Alcohol (67-56-1)	TLV-TWA	USA	200 ppm TWA	ACGIH - Threshold Limit Values - Time Weighted Averages (TLV-TWA)
Sodium Hydroxide (1310-73-2)	TWA	USA	2 mg/m³ TWA	U.S. - OSHA - Final PELs - Time Weighted Averages (TWAs)
Sodium Hydroxide (1310-73-2)	TLV-Ceiling	USA	2 mg/m³ Ceiling	ACGIH - Threshold Limit Values - Ceilings (TLV-C)

8.2. Exposure Controls

Engineering Controls: Use only outdoors or in a well-ventilated area. A system of local and/or general exhaust is recommended to keep employee exposures below the Airborne Exposure Limit.

Respiratory Protection: If engineering controls do not maintain airborne concentrations below recommended exposure limits, an approved atmosphere supplied respirator must be worn.

Skin Protection: Wear protective gloves and eye protection. Chemical resistant gloves.

Eye Protection: Wear protective gloves and eye protection. Safety glasses or goggles.

8.3. Personal Protective Equipment

Wear protective gloves and eye protection. If engineering controls do not maintain airborne concentrations below recommended exposure limits, an approved atmosphere supplied respirator must be worn. Chemical resistant gloves. Safety glasses or goggles.

SECTION 9: Physical and Chemical Properties

9.1. Basic Physical and Chemical Properties

Appearance: Colorless liquid

Physical State: Liquid

Odor: Data not available.

Odor Threshold: Data not available.

pH: > 13

Melting/Freezing Point: Data not available.

Initial Boiling Point /Range: Approximately 64.5°C - Approximately 64.5°C

Flash Point: Approximately 11°C

Evaporation Rate: 2.1 (butyl acetate = 1)

Flammability: Data not available.

Flammability/Explosive Limits: Data not available.

Vapor Pressure: Data not available.

Vapor Density: Data not available.

Relative Density: 0.8

Solubility: Data not available.

Partition Coeffieient (n-Octanol/Water): Data not available.

Auto-Ignition Temperature: Data not available.

Decomposition Temperature: Data not available.

Viscosity: Data not available.

ExplosiveProperties: Data not available.

Oxidizing Properties: Data not available.

SECTION 10: Stability and Reactivity

10.1. Reactivity and Chemical Stability

Stable under normal conditions of use and storage.

10.2. Possibility of Hazardous Reactions

Data not available.

10.3. Conditions to Avoid and Incompatible Materials

Keep away from heat, sparks and open flame. No smoking. Keep container tightly closed. Keep only in original container. Strong oxidizing agents

10.4. Hazardous Decomposition Products

Will not occur.

SECTION 11: Toxicological Information

11.1. Information on Toxicological Effects

Acute Toxicity - Oral Exposure:

Toxic if swallowed. Wash arms, hands and face thoroughly after handling. Do not eat, drink or smoke when using this product. IF SWALLOWED: Immediately call a POISON CENTER or physician. Specific treatment (Wash areas of contact with water immediately). Rinse mouth. Store locked up. Dispose of contents in accordance with local, state, federal and international regulations.

Acute Toxicity - Dermal Exposure:

Toxic in contact with skin. Wear protective gloves and eye protection. IF ON SKIN: Wash with plenty of soap and water. Call a POISON CENTER or physician if you feel unwell. Specific treatment (Wash areas of contact with water immediately). Take off immediately all contaminated clothing and wash it before reuse. Store locked up. Dispose of contents in accordance with local, state, federal and international regulations.

Acute Toxicity - Inhalation Exposure:

Toxic if inhaled. Avoid breathing dust, fumes or mist. Use only outdoors or in a well-ventilated area. IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or physician. Specific treatment (Wash areas of contact with water immediately). Store in a well-ventilated place. Keep container tightly closed. Store locked up. Dispose of contents in accordance with local, state, federal and international regulations.

Acute Toxicity - Other Information:

LD50, Oral, Rat: (Methanol) 5628 mg/kg, details of toxic effects not reported other than lethal dose value. Investigated as a mutagen (Sodium Hydroxide).

Skin Corrosion and Irritation:

Causes severe skin burns and eye damage. Do not breathe dust, fumes or mist. Wash arms, hands and face thoroughly after handling. Wear protective gloves and eye protection. IF SWALLOWED: rinse mouth. Do NOT induce vomiting. IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water. Wash contaminated clothing before reuse. IF INHALED: Remove person to fresh air and keep comfortable for breathing. Immediately call a POISON CENTER or physician. Specific treatment (Wash areas of contact with water immediately). IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Store locked up. Dispose of contents in accordance with local, state, federal and international regulations.

Serious Eye Damage and Irritation:

Causes serious eye damage. Wear protective gloves and eye protection. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER or physician.

Respiratory Sensitization:

Not applicable.

Skin Sensitization:

Not applicable.

Germ Cell Mutagenicity:

Not applicable.

Carcinogenicity:

Not applicable.

Reproductive Toxicity:

May damage fertility or the unborn child. Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Wear protective gloves and eye protection. IF exposed or concerned: Get medical attention. Store locked up. Dispose of contents in accordance with local, state, federal and international regulations.

Specific Target Organ Toxicity from Single Exposure:

Causes damage to organs. Do not breathe dust, fumes or mist. Wash arms, hands and face thoroughly after handling. Do not eat, drink or smoke when using this product. IF exposed: Call a POISON CENTER or physician. Specific treatment (Wash areas of contact with water immediately). Store locked up. Dispose of contents in accordance with local, state, federal and international regulations.

Specific Target Organ Toxicity from Repeated Exposure:

Causes damage to organs through prolonged or repeated exposure. Do not breathe dust, fumes or mist. Wash arms, hands and face thoroughly after handling. Do not eat, drink or smoke when using this product. Get medical attention if you feel unwell. Dispose of contents in accordance with local, state, federal and international regulations.

Aspiration Hazard:

Not applicable.

Additional Toxicology Information:

Data not available.

SECTION 12: Ecological Information

12.1. Ecotoxicity

Not applicable.

12.2. Persistence and Degradability

Data not available.

12.3. Bioaccumulative Potential

Data not available.

12.4. Mobility in Soil

Data not available.

12.5. Other Adverse Ecological Effects

Data not available.

Safety Data Sheet

SECTION 13: Disposal Considerations

13.1. Waste Treatment Methods

Data not available.

SECTION 14: Transportation Information

14.1. Transportation by Land - Department of Transportation (DOT, United States of America)

UN Number: UN2924

Proper Shipping Name: Flammable Liquid, Corrosive, n.o.s., (Methanol and Sodium Hydroxide)

Hazard Class: 3 (8)

Packing Group: II

Hazard Placard Labels:



14.2. Transportation by Air - International Air Transport Association (IATA)

UN Number: UN2924

Proper Shipping Name: Flammable Liquid, Corrosive, n.o.s., (Methanol and Sodium Hydroxide)

Hazard Class: 3 (8)

Packing Group: II

Hazard Placard Labels:



SECTION 15: Regulatory Information

15.1. Occupational Safety and Health Administration (OSHA) Hazards

Not listed.

15.2. Superfund Amendments and Reauthorization Act (SARA) 302 Extremely Hazardous Substances

Not listed.

15.3. Superfund Amendments and Reauthorization Act (SARA) 311/312 Hazardous Chemicals

Sodium Hydroxide (CAS # 1310-73-2): 1000 lb final RQ; 454 kg final RQ

Methyl Alcohol (CAS # 67-56-1): 5000 lb final RQ; 2270 kg final RQ

Safety Data Sheet

15.4. Superfund Amendments and Reauthorization Act (SARA) 313 Toxic Release Inventory (TRI)

Methyl Alcohol (CAS # 67-56-1): 1.0 % de minimis concentration

15.5. Massachusetts Right-to-Know Substance List

Sodium Hydroxide (CAS # 1310-73-2): Present
Methyl Alcohol (CAS # 67-56-1): Present

15.6. Pennsylvania Right-to-Know Hazardous Substances

Sodium Hydroxide (CAS # 1310-73-2): Environmental hazard
Sodium Hydroxide (CAS # 1310-73-2): Present
Methyl Alcohol (CAS # 67-56-1): Environmental hazard
Methyl Alcohol (CAS # 67-56-1): Present

15.7. New Jersey Worker and Community Right-to-Know Components

Sodium Hydroxide (CAS # 1310-73-2): corrosive
Sodium Hydroxide (CAS # 1310-73-2): sn 1706
Methyl Alcohol (CAS # 67-56-1): flammable - third degree; teratogen
Methyl Alcohol (CAS # 67-56-1): sn 1222
Methyl Alcohol (CAS # 67-56-1): SN 1222 TPQ: 500 lb

15.8. California Proposition 65

Methyl Alcohol (CAS # 67-56-1): developmental toxicity, initial date 3/16/12

15.9. Canada Domestic Substances List / Non-Domestic Substances List (DSL/NDSL)

Sodium Hydroxide (CAS # 1310-73-2): Present
Methyl Alcohol (CAS # 67-56-1): Present

15.10. United States of America Toxic Substances Control Act (TSCA) List

Sodium Hydroxide (CAS # 1310-73-2): Present
Methyl Alcohol (CAS # 67-56-1): Present

15.11. European Inventory of Existing Commercial Chemical Substances (EINECS), European List of Notified Chemical Substances (ELINCS), and No Longer Polymers (NLP)

Not listed.

Safety Data Sheet

SECTION 16: Other Information

16.1. Full Text of Hazard Statements and Precautionary Statements

Highly flammable liquid and vapor. May be corrosive to metals. Toxic if swallowed. Toxic in contact with skin. Causes severe skin burns and eye damage. Causes serious eye damage. Toxic if inhaled. May damage fertility or the unborn child. Causes damage to organs. Causes damage to organs through prolonged or repeated exposure.

Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Keep away from heat, sparks and open flame. No smoking. Keep only in original container. Ground container and receiving equipment. Use explosion-proof equipment. Use only non-sparking tools. Take precautionary measures against static discharge. Do not breathe dust, fumes or mist. Wash arms, hands and face thoroughly after handling. Do not eat, drink or smoke when using this product. Use only outdoors or in a well-ventilated area. Wear protective gloves and eye protection.

IF SWALLOWED: Immediately call a POISON CENTER or physician. IF ON SKIN: Wash with plenty of soap and water. IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water. IF INHALED: Remove person to fresh air and keep comfortable for breathing. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. IF exposed: Call a POISON CENTER or physician. Get medical attention if you feel unwell. Specific treatment (Wash areas of contact with water immediately). Wash contaminated clothing before reuse. In case of fire: Use dry chemical, foam or carbon dioxide to extinguish. Absorb spillage to prevent material damage.

Store in a well-ventilated place. Keep container tightly closed. Store in a well-ventilated place. Keep cool. Store locked up. Store in corrosive resistant container with a resistant inner liner.


Dispose of contents in accordance with local, state, federal and international regulations.

16.2. Miscellaneous Hazard Classes

Canadian Carcinogenicity Hazard Class: Not Applicable.
Physical Hazards Not Otherwise Classified (PHNOC): Not Applicable.
Health Hazards Not Otherwise Classified (HHNOC): Not Applicable.
Not Applicable.

16.3. National Fire Protection Association (NFPA) Rating

Health: 2
Flammability: 3
Reactivity: 0
Special Hazard:



Safety Data Sheet

16.4. Document Revision

Last Revision Date: 5/1/2015

DISCLAIMER

When handled properly by qualified personnel, the product described herein does not present a significant health or safety hazard. Alteration of its characteristics by concentration, evaporation, addition of other substances, or other means may present hazards not specifically addressed herein and which must be evaluated by the user. The information furnished herein is believed to be accurate and represents the best data currently available to us. No warranty, expressed or implied, is made and RICCA CHEMICAL COMPANY assumes no legal responsibility or liability whatsoever resulting from its use.