
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-353G

NB100-353G

BubR1 Antibody (8G1) [DyLight 488]



Unit Size
0.1 ml

Concentration
0.6 mg/ml

Storage
Store at 4C in the dark.

Applications
WB, ICC/IF

Species
Human, Mouse

Host
Mouse

Clonality
Monoclonal

Isotype
IgG1 Kappa

Conjugate
DyLight 488

Purity
Protein G purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
NB100-353 is specific for hBUBR1. There should be no cross-reactivity with hBUB1.

Immunogen
A portion of hBUBR1 tagged at the N-terminus with pMAL (residues 1-350 of human BUBR1).

Recommended Dilutions
immunofluorescence 1:100, Western Blot 1:2000 - 1:5000

Buffer
50mM sodium borate

Uses
By Western blot, this antibody recognizes a band at ~120 kDa, representing hBUBR1 protein. *The investigator should determine the optimal working dilution for a specific application.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-353G

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com