

	Revision Date 05/12/2014	Version 1.3
SECTION 1.Identification		
Product identifier		
Product number	101849	
Product name	tert-Butyl methyl ether for analysis EMSURE® ACS	
CAS-No.	1634-04-4	
Relevant identified uses of t	he substance or mixture and uses advised against	
Identified uses	Reagent for analysis	
Details of the supplier of the	safety data sheet	
Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 018 United States of America General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)	321,
Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International)	
	24 Hours/day; 7 Days/week	

SECTION 2. Hazards identification

GHS Classification

Flammable liquid, Category 2, H225 Skin irritation, Category 2, H315 For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word Danger

Hazard Statements H225 Highly flammable liquid and vapor. H315 Causes skin irritation.

Precautionary Statements

Product number	101849	Version 1.3
Product name	tert-Butyl methyl ether for analysis EMSURE® ACS	

P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.

P233 Keep container tightly closed.

P302 + P352 IF ON SKIN: Wash with plenty of soap and water.

P403 + P235 Store in a well-ventilated place. Keep cool.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200). This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS and may deviate from the GHS information.

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Chemical nature	Contains Methanol	
Formula	(as impurity) (CH₃)₃COCH₃	C₅H₁₂O (Hill)
Molar mass	88.15 g/mol	

Hazardous ingredients

Chemical Name (Concentration) CAS-No. *tert-butyl methyl ether (>= 90 % - <= 100 %)* 1634-04-4 Exact percentages are being withheld as a trade secret. *methanol (>= 0.1 % - < 1 %)* 67-56-1

Exact percentages are being withheld as a trade secret.

SECTION 4. First aid measures

Description of first-aid measures

Inhalation After inhalation: fresh air.

Skin contact After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eye contact

After eye contact: rinse out with plenty of water.

Ingestion

After swallowing: caution if victim vomits. Risk of aspiration! Keep airways free. Pulmonary failure possible after aspiration of vomit. Call a physician immediately.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

irritant effects, Dizziness, Unconsciousness, narcosis, agitation, spasms, euphoria, Nausea, Vomiting, drowziness, CNS disorders Drying-out effect resulting in rough and chapped skin.

Product number101849Product nametert-Butyl methyl ether for analysis EMSURE® ACS

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media Carbon dioxide (CO2), Foam, Dry powder

Unsuitable extinguishing media For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible. Vapors are heavier than air and may spread along floors. Forms explosive mixtures with air at ambient temperatures. Pay attention to flashback. Development of hazardous combustion gases or vapors possible in the event of fire.

Advice for firefighters

Special protective equipment for fire-fighters Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Prevent fire extinguishing water from contaminating surface water or the ground water system. Remove container from danger zone and cool with water.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Do not breathe vapors, aerosols. Avoid substance contact. Ensure adequate ventilation. Keep away from heat and sources of ignition. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains. Risk of explosion.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills. Observe possible material restrictions (see sections 7 and 10). Take up with liquid-absorbent material (e.g. Chemizorb®). Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Product number	101849	Version 1.3
Product name	tert-Butyl methyl ether for analysis EMSURE® ACS	

Advice on protection against fire and explosion

Keep away from open flames, hot surfaces and sources of ignition. Take precautionary measures against static discharge.

Conditions for safe storage, including any incompatibilities

Keep container tightly closed in a dry and well-ventilated place. Keep away from heat and sources of ignition. Protected from light.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)			
Basis	Value	Threshold limits	Remarks

tert-butyl methyl ether 1634-04-4ACGIHTime Weighted Average
(TWA):50 ppm

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment: Flame retardant antistatic protective clothing

Respiratory protection

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties		
Physical state	liquid	
Color	colorless	

duct number duct name	101849 tert-Butyl methyl ether for analysis EMSURE® ACS	Version 1
Odor	characteristic	
Odor Threshold	No information available.	
рН	not applicable	
Melting point	-108.6 °C	
Boiling point/boiling range	131.5 °F (55.3 °C) at 1,013 hPa	
Flash point	-18 °F (-28 °C) Method: c.c.	
Evaporation rate	No information available.	
Flammability (solid, gas)	No information available.	
Lower explosion limit	1.5 %(V)	
Upper explosion limit	8.5 %(V)	
Vapor pressure	ca.268 hPa at 68 °F (20 °C)	
Relative vapor density	No information available.	
Density	ca.0.74 g/cm³ at 68 °F (20 °C)	
Relative density	No information available.	
Water solubility	ca.42 g/l at 68 °F (20 °C)	
Partition coefficient: n- octanol/water	log Pow: 1.06 OECD Test Guideline 107 Bioaccumulation is not expected.	
Autoignition temperature	No information available.	
Decomposition temperature	No information available.	
Viscosity, dynamic	0.36 mPa.s at 68 °F (20 °C)	
Explosive properties	Not classified as explosive.	
Oxidizing properties	none	

Product number	101849	Version 1.3
Product name	tert-Butyl methyl ether for analysis EMSURE® ACS	

Ignition temperature

860 °F (460 °C) Method: DIN 51794

SECTION 10. Stability and reactivity

Reactivity

Vapors may form explosive mixture with air. Formation of peroxides possible.

Chemical stability

Sensitivity to light

Possibility of hazardous reactions

Violent reactions possible with:

Oxidizing agents, Strong acids, halogens, Strong bases

Conditions to avoid

Warming.

Incompatible materials

rubber, various plastics

Hazardous decomposition products

Peroxides

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure Inhalation, Eye contact, Skin contact

Acute oral toxicity LD50 rat: > 2,000 mg/kg OECD Test Guideline 401

Symptoms: Nausea, Vomiting, Pulmonary failure possible after aspiration of vomit., Aspiration may cause pulmonary edema and pneumonitis.

Acute inhalation toxicity LC50 rat: 85 mg/l; 4 h (IUCLID)

Symptoms: Possible damages:, mucosal irritations

Acute dermal toxicity LD50 rabbit: > 2,000 mg/kg OECD Test Guideline 402

absorption

Product number	101849	Version 1.3
Product name	tert-Butyl methyl ether for analysis EMSURE® ACS	
<i>Skin irritation</i> rabbit Result: Irritations OECD Test Guideline 404		
Drying-out effect resulting in ro Causes skin irritation.	ough and chapped skin.	
<i>Eye irritation</i> rabbit Result: No eye irritation OECD Test Guideline 405		
<i>Sensitization</i> Sensitization test (Magnusson Result: negative (IUCLID)	and Kligman):	
<i>Genotoxicity in vitro</i> Mutagenicity (mammal cell tes Result: negative (IUCLID)	st): micronucleus.	
Ames test Result: negative Method: OECD Test Guideline	e 471	
<i>Specific target organ systemic</i> The substance or mixture is n	<i>c toxicity - single exposure</i> ot classified as specific target organ toxicant, single exposure.	
<i>Specific target organ systemic</i> The substance or mixture is n	<i>c toxicity - repeated exposure</i> ot classified as specific target organ toxicant, repeated exposure.	
<i>Aspiration hazard</i> Regarding the available data	the classification criteria are not fulfilled.	
Carcinogenicity		
IARC	No ingredient of this product present at levels greater than or	
	equal to 0.1% is identified as probable, possible or confirmed	
	human carcinogen by IARC.	
OSHA	No ingredient of this product present at levels greater than or	
	equal to 0.1% is identified as a carcinogen or potential	
	carcinogen by OSHA.	
NTP	No ingredient of this product present at levels greater than or	
	equal to 0.1% is identified as a known or anticipated carcinogen	
	by NTP.	
ACGIH	Confirmed animal carcinogen with unknown relevance to	
	humans.	
	tert-butyl methyl ether 1634-04-4	

Further information

Systemic effects:

After absorption of large quantities:

Product number	101849
Product name	tert-Butyl methyl ether for analysis EMSURE® ACS

drowziness, Dizziness, euphoria, agitation, spasms, CNS disorders, Unconsciousness, narcosis Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

Toxicity to fish LC50 Pimephales promelas (fathead minnow): 672 mg/l; 96 h (IUCLID)

Toxicity to daphnia and other aquatic invertebrates EC50 Daphnia magna (Water flea): 651 mg/l; 48 h (IUCLID)

Toxicity to algae

IC50 Desmodesmus subspicatus (green algae): > 800 mg/l; 72 h (IUCLID)

Toxicity to bacteria

EC10 Pseudomonas putida: ca. 700 mg/l; 18 h (IUCLID)

Persistence and degradability

Biodegradability 2 %; 28 d OECD Test Guideline 301B Not readily biodegradable.

Bioaccumulative potential

Partition coefficient: n-octanol/water log Pow: 1.06 OECD Test Guideline 107 Bioaccumulation is not expected.

Mobility in soil

No information available.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)	
UN number	UN 2398
Proper shipping name	METHYL TERT-BUTYL ETHER
Class	3
Packing group	II
Environmentally hazardous	
Air transport (IATA)	

Product number	101849	Version 1.3
Product name	tert-Butyl methyl ether for analysis EMSURE® ACS	
UN number	UN 2398	
Proper shipping name	METHYL TERT-BUTYL ETHER	
Class	3	
Packing group	II	
Environmentally hazardous		
Special precautions for user	no	
Sea transport (IMDG)		
UN number	UN 2398	
Proper shipping name	METHYL TERT-BUTYL ETHER	
Class	3	
Packing group	II	
Environmentally hazardous		
Special precautions for user EmS	yes F-E S-D	

SECTION 15. Regulatory information

United States of America

OSHA Hazards Flammable Liquid Skin irritant

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Fire Hazard Acute Health Hazard

SARA 313

The following components are subject to reporting levels established by SARA Title III, Section 313:313:Ingredientstert-butyl methyl ether1634-04-498.0001 %

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Product number	101849	Version 1	. 3
Product name	tert-Butyl methyl ether for analysis EMSURE® ACS		

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311,

Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311,

Table 117.3.

DEA List I Not listed

DEA List II Not listed

US State Regulations

Massachusetts Right To Know

Ingredients tert-butyl methyl ether

Pennsylvania Right To Know

Ingredients tert-butyl methyl ether

New Jersey Right To Know

Ingredients tert-butyl methyl ether methanol

California Prop 65 Components

WARNING: This product contains a chemical known in the State of California to cause birth defects or other reproductive harm. *Ingredients* methanol **Notification status**

TSCA:	All components of the product are listed in the TSCA-inventory.
DSL:	All components of this product are on the Canadian DSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H225	Highly flammable liquid and vapor.
H315	Causes skin irritation.

Key or legend to abbreviations and acronyms used in the safety data sheet Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Product number 101849 Product name tert-Butyl methyl ether for analysis EMSURE® ACS

Revision Date 05/12/2014

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.