

according to the Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 08/16/2012

Version 1.2

### **SECTION 1. Identification**

#### Product identifier

Product number 109057

Product name Hydrochloric acid c(HCI) = 1 mol/l (1 N) TitriPUR®

## Relevant identified uses of the substance or mixture and uses advised against

Identified uses Reagent for analysis

## Details of the supplier of the safety data sheet

Company EMD Millipore Corporation | 290 Concord Road, Billerica, MA 01821,

United States of America | SDS Phone Support: +1-978-715-1335 | General Inquiries: +1-978-751-4321 | Monday to Friday, 9:00 AM to

4:00 PM Eastern Time (GMT-5)

e-mail: mm\_sds@merckgroup.com

Emergency telephone 800-424-9300 CHEMTREC (USA)

+1-703-527-3887 CHEMTREC (International)

24 Hours/day; 7 Days/week

### SECTION 2. Hazards identification

### **GHS Classification**

Corrosive to Metals, Category 1, H290

For the full text of the H-Statements mentioned in this Section, see Section 16.

# **GHS-Labeling**

Hazard pictograms



Signal Word Warning

Hazard Statements

H290 May be corrosive to metals.

## **OSHA Hazards**

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number 109057 Version 1.2

Product name Hydrochloric acid c(HCl) = 1 mol/l (1 N) TitriPUR®

1910.1200).

#### Other hazards

None known.

## SECTION 3. Composition/information on ingredients

Chemical nature Aqueous solution

#### Hazardous ingredients

Chemical Name ( Concentration)

CAS-No.

hydrochloric acid ( >= 1 % - < 5 % )

7647-01-0

#### SECTION 4. First aid measures

### Description of first-aid measures

Inhalation

After inhalation: fresh air.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eve contact

After eye contact: rinse out with plenty of water with the eyelid held wide open. Call in ophthalmologist if necessary.

Inaestion

After swallowing: make victim drink water (two glasses at most). Consult doctor if feeling unwell.

Never give anything by mouth to an unconscious person.

# Most important symptoms and effects, both acute and delayed

irritant effects

### Indication of any immediate medical attention and special treatment needed

No information available.

## SECTION 5. Fire-fighting measures

# Extinguishing media

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

## Special hazards arising from the substance or mixture

Not combustible.

Ambient fire may liberate hazardous vapors.

Fire may cause evolution of:

Hydrogen chloride gas

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number 109057 Version 1.2

Product name Hydrochloric acid c(HCI) = 1 mol/I (1 N) TitriPUR®

# Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

#### SECTION 6. Accidental release measures

## Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Do not breathe vapors, aerosols. Avoid substance contact. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

### **Environmental precautions**

Do not empty into drains.

#### Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent and neutralizing material (e.g. Chemizorb® H\*, Merck Art. No.

101595). Dispose of properly. Clean up affected area.

## SECTION 7. Handling and storage

## Precautions for safe handling

Observe label precautions.

# Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers

No metal containers.

Tightly closed.

Store at +15°C to +25°C (+59°F to +77°F).

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number 109057 Version 1.2

Product name Hydrochloric acid c(HCl) = 1 mol/l (1 N) TitriPUR®

## SECTION 8. Exposure controls/personal protection

## Exposure limit(s)

Ingredients

Basis Value Threshold Remarks

limits

hydrochloric acid 7647-01-0

ACGIH Ceiling Limit Value: 2 ppm

NIOSH/GUIDE Ceiling Limit Value and 5 ppm
Time Period (if 7 mg/m³

specified):

OSHA\_TRANS Ceiling Limit Value: 5 ppm 7 mg/m³

Z1A Ceiling Limit Value: 5 ppm

7 mg/m³

#### **Engineering measures**

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

#### Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

### Hygiene measures

Change contaminated clothing. Application of skin- protective barrier cream recommended.

Wash hands after working with substance.

Eye/face protection

Safety glasses

# Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

#### Recommended:

full contact:

Glove material: Nitrile rubber Glove thickness: 0.11 mm Break through time: > 480 min

splash contact:

Glove material: Nitrile rubber Glove thickness: 0.11 mm Break through time: > 480 min

Other protective equipment:

protective clothing

Respiratory protection

required when vapors/aerosols are generated.

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number 109057 Version 1.2

Product name Hydrochloric acid c(HCl) = 1 mol/l (1 N) TitriPUR®

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

# SECTION 9. Physical and chemical properties

Physical state liquid

Color colorless

Odor odorless

Odor Threshold not applicable

pH < 1

at 68 °F ( 20 °C)

Melting point No information available.

Boiling point No information available.

Flash point No information available.

Evaporation rate No information available.

Flammability (solid, gas) not applicable

Lower explosion limit No information available.

Upper explosion limit No information available.

Vapor pressure No information available.

Relative vapor density No information available.

Relative density 1.02 g/cm<sup>3</sup>

at 68 °F ( 20 °C)

Water solubility at 68 °F ( 20 °C)

soluble

Partition coefficient: n-

octanol/water

No information available.

Autoignition temperature No information available.

Decomposition temperature No information available.

Viscosity, dynamic No information available.

Corrosion May be corrosive to metals.

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number 109057 Version 1.2

Product name Hydrochloric acid c(HCI) = 1 mol/I (1 N) TitriPUR®

## SECTION 10. Stability and reactivity

#### Reactivity

See below

#### Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

## Possibility of hazardous reactions

Generates dangerous gases or fumes in contact with:

Metals

Violent reactions possible with:

The generally known reaction partners of water.

#### Conditions to avoid

no information available

# Incompatible materials

Metals, metal alloys

#### Hazardous decomposition products

in the event of fire: See section 5.

# SECTION 11. Toxicological information

## Information on toxicological effects

Likely route of exposure

Eye contact, Skin contact

Target Organs

Eyes

Skin

Respiratory system

Cornea

Acute inhalation toxicity

LC50 rat: 3124 ppm; 1 h (calculated on the pure substance) (RTECS)

Skin irritation

slight irritation

Eye irritation

slight irritation

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number 109057 Version 1.2

Product name Hydrochloric acid c(HCl) = 1 mol/l (1 N) TitriPUR®

Carcinogenicity

IARC No ingredient of this product present at levels greater than or

equal to 0.1% is identified as probable, possible or confirmed

human carcinogen by IARC.

OSHA No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential

carcinogen by OSHA.

NTP No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a known or anticipated carcinogen

by NTP.

ACGIH No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential

carcinogen by ACGIH.

#### **Further information**

Handle in accordance with good industrial hygiene and safety practice.

# **SECTION 12. Ecological information**

#### **Ecotoxicity**

No information available.

# Persistence and degradability

No information available.

### Bioaccumulative potential

No information available.

#### Mobility in soil

No information available.

## Other adverse effects

Additional ecological information

Discharge into the environment must be avoided.

#### **SECTION 13. Disposal considerations**

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number 109057 Version 1.2

Product name Hydrochloric acid c(HCl) = 1 mol/l (1 N) TitriPUR®

# **SECTION 14. Transport information**

Land transport (DOT)

UN number UN 1789

Proper shipping name HYDROCHLORIC ACID

Class 8

Packing group III

Environmentally hazardous --

Air transport (IATA)

UN number UN 1789

Proper shipping name HYDROCHLORIC ACID

Class 8

Packing group III

Environmentally hazardous --

Special precautions for user no

Sea transport (IMDG)

UN number UN 1789

Proper shipping name HYDROCHLORIC ACID

Class 8

Packing group III

Environmentally hazardous --

Special precautions for user yes

EmS F-A S-B

# SECTION 15. Regulatory information

**United States of America** 

**OSHA Hazards** 

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number 109057 Version 1.2

Product name Hydrochloric acid c(HCl) = 1 mol/l (1 N) TitriPUR®

Target organ effects Corrosive to skin Corrosive to eyes Toxic by inhalation.

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

Target organ effects Corrosive to skin Corrosive to eyes Respiratory irritant

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

#### SARA 311/312 Hazards

Acute Health Hazard Chronic Health Hazard

# **US State Regulations**

# Massachusetts Right To Know

*Ingredients* hydrochloric acid

## Pennsylvania Right To Know

Ingredients
water
hydrochloric acid

## **New Jersey Right To Know**

Ingredients
water
hydrochloric acid

# California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

### **Notification status**

according to the Hazard Communication Standard (29 CFR 1910.1200)

Product number 109057 Version 1.2


Product name Hydrochloric acid c(HCl) = 1 mol/l (1 N) TitriPUR®

TSCA: On TSCA Inventory

DSL: All components of this product are on the Canadian DSL list.

## SECTION 16. Other information

# National Fire Protection Association (U.S.A)



## Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H290 May be corrosive to metals.

# Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.