

MATERIAL SAFETY DATA SHEET

Cat# K820-50, -500, ECL Western Blotting Substrate

MSDS DATE: 7May2015

SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: ECL Western Blotting Substrate
PRODUCT CODES: Cat# K820-50, -500
MANUFACTURER: BioVision, Inc.
DIVISION:
ADDRESS: 155 South Milpitas Blvd., Milpitas, CA 95035
EMERGENCY PHONE: 858-373-8066
CHEMTREC PHONE:
OTHER CALLS: 408-493-1800
FAX PHONE: 408-493-1801

SECTION 2: COMPOSITION/INFORMATION ON INGREDIENTS

Component	Description	Volume	Safety Information
Reagent A	Proprietary Solution	K820-50: 25 ml K820-500: 250 ml	No hazards
Reagent B	Proprietary Solution	K820-50: 25 ml K820-500: 250 ml	No hazards

SECTION 3: HAZARDS IDENTIFICATION

Emergency Overview

GHS Classification: Not a dangerous substance according to GHS

GHS Label elements, including precautionary statements

Pictogram: none

Signal word: none

Hazard statement(s): none

Precautionary statement(s): none

HMIS Classification

Health hazard: 0

Flammability: 0

Physical hazards: 0

NFPA Rating

Health Hazard: 0

Fire: 0

Reactivity Hazard: 0

Potential Health Effects

Inhalation: May be harmful if inhaled. May cause respiratory tract irritation.

Skin: May be harmful if absorbed through skin. May cause skin irritation.

Eyes: May cause eye irritation.

Ingestion: May be harmful if swallowed.

SECTION 4: FIRST AID MEASURES

General advice: Consult a physician. Show this safety data sheet to the doctor in attendance. Move out of dangerous area.

If inhaled: If breathed in, move person into fresh air. If not breathing, give artificial respiration. Consult a physician.

In case of skin contact: Take off contaminated clothing and shoes immediately. Wash off with soap and plenty of water. Consult a physician.

In case of eye contact: Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician. Continue rinsing eyes during transport to hospital.

If swallowed: DO NOT induce vomiting. Never give anything by mouth to an unconscious person. Rinse mouth with water. Consult a physician.

SECTION 5: FIRE-FIGHTING MEASURES

Condition of flammability: Not flammable or combustible.

Suitable extinguishing media: Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.

Special protective equipment for fire-fighters: Wear self-contained breathing apparatus for firefighting if necessary.

Hazardous combustion products: Hazardous decomposition products formed under fire conditions— see section 10.

SECTION 6: ACCIDENTAL RELEASE MEASURES

Personal precautions: Use personal protective equipment. Avoid dust formation. Avoid breathing vapors, mist or gas. Ensure adequate ventilation. Evacuate personnel to safe areas. Avoid breathing dust.

Environmental precautions: Do not let product enter drains.

MATERIAL SAFETY DATA SHEET

Cat# K820-50, -500, ECL Western Blotting Substrate

MSDS DATE: 7May2015

Methods for cleaning up: Pick up and arrange disposal without creating dust. Sweep up and shovel. Keep in suitable, closed containers for disposal.

SECTION 7: HANDLING AND STORAGE

Precautions for safe handling

Avoid contact with skin and eyes. Avoid formation of dust and aerosols. Provide appropriate exhaust ventilation at places where dust is formed. Normal measures for preventive fire protection.

Conditions for safe storage

Keep container tightly closed in a dry and well-ventilated place.
Recommended storage temperature: +4 °C.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

Contains no substances with occupational exposure limit values.

Personal protective equipment

Respiratory protection

Where risk assessment shows air-purifying respirators are appropriate use a full-face respirator with multi-purpose combination (US) or type ABEK (EN 14387) respirator cartridges as a backup to engineering controls. If the respirator is the sole means of protection, use a full-face supplied air respirator. Use respirators and components tested and approved under appropriate government standards such as NIOSH (US) or CEN (EU).

Hand protection

Handle with gloves. Gloves must be inspected prior to use. Use proper glove removal technique (without touching glove's outer surface) to avoid skin contact with this product. Dispose of contaminated gloves after use in accordance with applicable laws and good laboratory practices. Wash and dry hands.

Eye protection

Tightly fitting safety goggles. Face shield (8-inch minimum). Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU).

Skin and body protection

Complete suit protecting against chemicals. The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.

Hygiene measures

Handle in accordance with good industrial hygiene and safety practice. Wash hands before breaks and at the end of workday.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Property	Western Blot ECL Substrate
Appearance:	No data available
pH:	No data available
Water Solubility:	No data available
Other Solubility:	No data available
Specific Gravity (g/ml):	No data available
Boiling Point (°C):	No data available
Melting Point (°C):	No data available
Flash Point (°C):	No data available
Ignition Temperature (°C):	No data available
Density	No data available

SECTION 10: STABILITY AND REACTIVITY

Property	Western Blot ECL Substrate
Appearance:	No data available
pH:	No data available
Water Solubility:	No data available
Other Solubility:	No data available
Specific Gravity (g/ml):	No data available
Boiling Point (°C):	No data available
Melting Point (°C):	No data available
Flash Point (°C):	No data available
Ignition Temperature (°C):	No data available
Density	No data available

SECTION 11: TOXICOLOGICAL INFORMATION

Western Blot ECL Substrate

Acute toxicity: no data available

Skin corrosion/irritation: no data available

Serious eye damage/eye irritation: no data available

Respiratory or skin sensitization: no data available

MATERIAL SAFETY DATA SHEET

Cat# K820-50, -500, ECL Western Blotting Substrate

MSDS DATE: 7May2015

Germ cell mutagenicity: no data available

Carcinogenicity:

- IARC: 3 – Group 3: Not classifiable as to its carcinogenicity to humans (Hydrogen peroxide)
ACGIH: No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.
NTP: No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
OSHA: No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.

Reproductive toxicity: no data available

Teratogenicity: no data available

Specific target organ toxicity – single exposure (GHS): no data available

Specific target organ toxicity – repeated exposure (GHS): no data available

Aspiration hazard: no data available

Potential Health Effects

Inhalation: May be harmful if inhaled. Material is extremely destructive to the tissue of the mucous membranes and upper respiratory tract.

Skin: May be harmful if absorbed through skin. Causes skin burns.

Eyes: Causes eye burns.

Ingestion: Harmful if swallowed.

Signs and Symptoms of Exposure: To the best of our knowledge, the chemical, physical, and toxicological properties have not been thoroughly investigated.

Additional information: RTECS: not available

SECTION 12: ECOLOGICAL INFORMATION

Western Blot ECL Substrate:

Persistence and degradability: no data available

Toxicity: no data available

Bioaccumulative potential: no data available

Mobility in soil: no data available

PBT and vPvB assessment: no data available

Other adverse effects: An environmental hazard cannot be excluded in the event of unprofessional handling or disposal.

Harmful to aquatic life.

SECTION 13: DISPOSAL CONSIDERATIONS

Product: Offer surplus and non-recyclable solutions to a licensed disposal company. Contact a licensed professional waste disposal service to dispose of this material. Dissolve or mix the material with a combustible solvent and burn in a chemical incinerator equipped with an afterburner and scrubber.

Contaminated packaging: Dispose of as unused product.

SECTION 14: TRANSPORT INFORMATION

DOT (US): Not dangerous goods.

IMDG: Not dangerous goods.

IATA: Not dangerous goods.

SECTION 15: REGULATORY INFORMATION

OSHA Hazards: No known OSHA hazards

SARA 302 Components: SARA 302: No chemical in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 Components: SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title II, Section 313.

SARA 311/312 Hazards: No SARA Hazards

Massachusetts Right To Know Components: No components are subject to the Massachusetts Right to Know Act.

Pennsylvania Right To Know Components: No components are subject to the Pennsylvania Right to Know Act.

New Jersey Right To Know Components: No components are subject to the New Jersey Right to Know Act.

California Prop. 65 Components: This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

EU regulations: This product is not classified according to the EU regulations.

SECTION 16: OTHER INFORMATION

DISCLAIMER:

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. The information in this document is based on the present state of our knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product. BioVision, Inc., shall not be held liable for any damage resulting from handling or from contact with the above product. See reverse side of invoice or packing slip for additional terms and conditions of sale.