

Datasheet

RHOH polyclonal antibody (A01)

transcribed only in hemopoietic cells. [provided by RefSeq]

Catalog Number: H00000399-A01

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a full-length recombinant RHOH.

Immunogen: RHOH (AAH14261.1, 1 a.a. ~ 191 a.a) full-length recombinant protein with GST tag.

Sequence:

MLSSIKCVLVGDSAVGKTSLLVRFTSETFPEAYKPTVY
ENTGVDVFMGDIQISLGLWDTAGNDAFRSIRPLSYQQ
ADVLMCYSVANHNSFLNLKNKWIGEIRSNLPCTPVLV
VVTQTDQREMGPFRASCVNAMEGKKLAQDVRAKGYL
ECSALSNRGVQQVFECVRTAVNQARRRNRRRLFSIN
ECKIF

Host: Mouse

Reactivity: Human

Applications: ELISA, WB-Re

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: 50 % glycerol

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 399

Gene Symbol: RHOH

Gene Alias: ARHH, TTF

Gene Summary: The protein encoded by this gene is a member of the Ras superfamily of small GTPases. Expression of a chimeric transcript of LAZ3 and this gene has been reported as a result of the translocation t(3;4) in non-Hodgkin's lymphomas. This gene encodes a small G-like protein, and unlike most other small G proteins which are expressed ubiquitously, this gene is